

2-Post 6U Heavy-Duty Wall-Mount Network Rack, 19" Open Frame Server Rack, 18" Deep, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts & Screws Included

**Product ID:** RK619WALLO



This open-frame 6U wall mount rack provides 6U of storage, allowing you to save space and stay organized. The 19 inch equipment rack can hold up to 175 lb. (80 kg).

The wall mount open frame rack is 18 in. (45.7 cm) deep, so it's perfect for smaller spaces. It ships fully assembled and features mounting holes that are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

You can mount the wall mount open frame rack where space is limited, such as on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

By having an open frame, the small wall mount network rack provides passive cooling to equipment. Additionally, the open frame provides easy access and configurability to your equipment, allowing you to maximize productivity.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RK619WALLO is backed by a StarTech.com a lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mounting audio video broadcast or distribution components

## Features

- **2-POST 6U WALL MOUNT NETWORK RACK:** EIA/ECA-310 compliant open frame server rack with 17.1" (43,5cm) mounting depth is ideal for installing IT / AV / Data equipment, patch panels, switches and shelves in small spaces
- **HEAVY DUTY:** This heavy duty 2 post open frame rack supports unobstructed airflow and is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 176lbs (80Kg) of equipment
- **FULLY ASSEMBLED:** The IT server rack ships fully assembled with all of the rack screws and cage nuts required to mount your equipment; Wall Mount Data Rack is EIA/ECA-310-E Compliant
- **HARDWARE INCLUDED:** The 2 post open frame wall mount server rack includes a complete set of M6 square cage nuts, M6 screws, and hook and loop to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 6U open frame wall mount rack is backed for 5 years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

|                       |   |
|-----------------------|---|
| Warranty              | Lifetime                                |
| Wallmountable         | Yes                                     |
| Rack Type             | 2-Post                                  |
| Frame Type            | Open Frame                              |
| U Height              | 6U                                      |
| Special Features      | Ships Fully Assembled<br>Wall-Mountable |
| Mounting Rail Profile | G-Shape                                 |
| Mounting Hole Types   | Square (For Cage Nut)                   |
| Industry Standards    | EIA/ECA-310-E                           |

---

### Performance

|                 |                  |
|-----------------|------------------|
| Weight Capacity | 176.4 lb [80 kg] |
|-----------------|------------------|

**Physical  
Characteristics**

Color                    Black

Construction Material                    Steel

---

**Product  
Measurements**

Product Length                    18.0 in [45.7 cm]

Product Width                    21.9 in [55.5 cm]

Product Height                    16.0 in [40.7 cm]

Weight of Product                    23.2 lb [10.5 kg]

Maximum Mounting Depth                    17.1 in [43.5 cm]

---

**Packaging  
Information**

Flat Pack (Assembly  
Required)                    No

Package Length                    21.3 in [54.1 cm]

Package Width                    25.1 in [63.7 cm]

Package Height                    19.7 in [50.1 cm]

Shipping (Package)  
Weight                    25.2 lb [11.4 kg]

---

**What's in the Box**

Included in Package                    1 - Rack

24 - M6 Screw

24 - M6 Cage Nuts

1 - 10 Foot Length Roll of Black Hook and Loop

---

**Warranty  
Information**

Warranty                    Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*