

2-Post 8U Heavy-Duty Wall Mount Network Rack, 19" Open Frame Server Rack with Adjustable Depth, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts and Screws Included

Product ID: RK812WALLOA



The RK812WALLOA 8U Open Frame Wall Mount Equipment Rack with Adjustable Depth is a high-quality, sturdy relay rack solution that is easy to assemble and install into any environment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The open rack features an adjustable depth ranging from 12-20 inches, in order to accommodate larger data, network and telecommunications devices. The greater than average depth of the rack also allows for mounting of shelves and other accessories. The wall mounts are positioned 16in apart (center to center), making it suitable for mounting on virtually any wall surface, based on North American wall frame stud spacing standards.

This 8U rack can be mounted to the wall in a server room, office, or above a doorway, expanding your workspace and keeping your equipment easily accessible.

Backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility



## Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Mount Audio/Video broadcast or distribution components

- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

## Features

- **ADJUSTABLE DEPTH:** This 2-post 8U 19 inch open frame network rack is EIA/ECA-310 compliant and has an adjustable depth (12-20in / 30.5-50.8cm); Data rack is ideal for AV / Audio / IT / computer equipment, servers, switches, patch panels, and PDUs
- **HEAVY DUTY:** Durable rack features a vertical rail made of SPCC cold-rolled steel and a weight capacity of up to 135lbs/60kg; Its design supports unobstructed airflow to help keep your equipment cool and easy to install with access to all sides
- **EFFICIENT FLAT PACK SHIPPING:** The IT rack ships flat packed with ISTA-6 certified packaging (assembly required) to ensure hassle-free installations with complete & undamaged delivery; Comprehensive assembly instructions included
- **HARDWARE INCLUDED:** The open post wall mount server rack includes a complete set of M5 square cage nuts, M5 screws and plastic washers to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 8U wall mounted network rack is backed for 5-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	8U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	135.0 lb [61.2 kg]
-----------------	--------------------

---

### Special Notes /

**Requirements**

Note	Hardware to mount the rack to the wall is not provided
------	--

---

**Physical Characteristics**

Color	Black
Construction Material	Steel

---

**Product Measurements**

Product Length	12.0 in [30.5 cm]
Product Width	19.8 in [50.4 cm]
Product Height	17.9 in [45.5 cm]
Weight of Product	24.6 lb [11.2 kg]
Maximum Mounting Depth	20.0 in [50.8 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	17.5 in [44.5 cm]
Package Width	25.1 in [63.7 cm]
Package Height	23.6 in [59.9 cm]
Shipping (Package) Weight	28.9 lb [13.1 kg]

---

**What's in the Box**

Included in Package	1 - Wall Mount Rack
	16 - Assembly Screws
	16 - M5 Screws
	16 - M5 Cage Nuts
	16 - Truss Head Screws
	1 - Installation Guide

---

**Warranty**

**Information**

Warranty      Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***

