

2-Post 8U Desktop Server Rack, Small Open Frame 19in Computer Rack, Compact Network Rack for AV / Studio / Data / IT Equipment - Free Standing Two-Post Home/Office Rack - TAA

Product ID: RK8OD



This 2-post desktop rack provides 8U of storage space for mounting smaller A/V and IT equipment.

With this 2-post rack, you can mount equipment at a fraction of the cost of conventional racks. The lightweight rack is engineered to meet EIA-310 rack-mount standards and is constructed of solid steel, ensuring a sturdy and safe mounting solution for your mission-critical equipment.

The rack features an open frame, free standing design that saves space with a small footprint. It gives you the ability to place rack-mount equipment on any surface in your office, such as your desk. This makes it easy to access your equipment on a daily basis.

The 2-post rack is easy to assemble and includes a pack of 20 M5 screws and cage nuts.

If you're looking for a desktop mounting solution with more rack units, StarTech.com also offers a 12U 2-post desktop rack.

The RK8OD is backed by a StarTech.com lifetime warranty and free technical support.

Certifications, Reports and Compatibility



Applications

- Place KVMs and rack-mount computers or server systems neatly on or beside your desk

- Save space in your SoHo (small office, home office) or server room, by placing equipment on desk or other surface, instead of taking up floor space

Features

- 2-POST 8U DESKTOP SERVER RACK: Open frame rack for 19" rackmount networking / AV / media / IT equipment; Ideal for use on a workbench or small home/office spaces without dedicated wiring closets
- DESIGNED FOR EASY ACCESS: This mini free standing network rack is 16.1in (41cm) in height with a compact profile, and is ideal for environments where frequent front and rear access to equipment is required
- TECH SPECS: 8U Open Frame Rack; 19in Wide; 2 Post; EIA/ECA-310-E Compliant; Units (U) Heights Marked; 110.2lb (50kg) Capacity; M5 Cage nuts and screws included.
- EASY SHIPPING AND ASSEMBLY: Compact flat pack shipping/packaging design to avoid damage and facilitate problem-free installations; Quick and easy setup on a desk, table or floor in your home/office; Ships with cage nuts and screws for mounting equipment
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this 2-Post 8U Desktop Open-Frame Rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	2-Post
Frame Type	Open Frame
U Height	8U
Special Features	Easy Assembly
	U-Markings
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	110.2 lb [50 kg]
-----------------	------------------

Physical Characteristics

Color	Black
-------	-------

Construction Material Steel

Product Measurements

Product Length	19.6 in [49.8 cm]
Product Width	11.6 in [29.5 cm]
Product Height	16.1 in [40.9 cm]
Weight of Product	4.8 lb [2.2 kg]
Maximum Mounting Depth	11.4 in [29.0 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	21.7 in [55.0 cm]
Package Width	4.2 in [10.6 cm]
Package Height	4.9 in [12.4 cm]
Shipping (Package) Weight	5.3 lb [2.4 kg]

What's in the Box

Included in Package	1 - Left Base Bracket
	1 - Right Base Bracket
	1 - Left Vertical Rail
	1 - Right Vertical Rail
	1 - Front Base Bracket
	4 - Rubber Feet
	8 - Assembly Screws
	20 - M5 Screws
	20 - M5 Cage Nuts
	1 - Instruction Manual

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

