

Rackmount KVM Console - Single Port VGA KVM with 17" LCD Monitor for Server Rack - Fully Featured Universal 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

Product ID: RKCONS1701



Providing centralized control of your PC, server, or KVM switch, this single-port rackmount KVM console gives you easy access to your connected system. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rack space.

The 1U rackmount console features a built-in keyboard (QWERTY), a touchpad for intuitive control, and a 17-inch LCD display that supports resolutions up to 1280x1024.

This single-port KVM console includes everything you need to set up right out of the box:

- 1 VGA KVM Cable
- Mounting Rails
- M5 Cage Nuts and Screws

The rack console features a single-port KVM module, which can be connected directly to a server or PC, or to a KVM switch for access to multiple systems. The KVM module offers the flexibility you need for easily integrating the console into your existing server infrastructure.

Rack consoles provide convenient, rack-mounted control options for single servers or entire server rooms. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. RKCONS1701 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

Features

- **FLEXIBLE DESIGN:** This rackmount KVM console drawer works with all KVM switch brands and models that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- **VERSATILE INTERFACES:** Rack mount monitor w/ 17" Active Matrix TFT 1280 x 1024 LCD 1U height 99 key full keyboard with numeric keypad + Trackpad Supports VGA and USB Integrated Power Supply
- **MAX DURABILITY:** Features durable steel housing design and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 50,000 hour MTBF
- **TESTED AND PROVEN:** Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product
- **KVM Collection:** Can be purchased with integrated 8-port (RKCONS1708K) or 16-port (RKCONS1716K) KVM or use with StarTech.com enterprise KVM switches: SV831DUSB, SV831DUSBUK, SV1631DUSBU, SV1631DUSBUK.

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	No
Audio	No
Display Size	17"
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB
PC Video Type	VGA

Number of Monitors Supported 1

Rack-Mountable Yes

Cables Included Yes

Performance

On-Screen Display Yes

IP Control No

Maximum Analog Resolutions 1280 x 1024

Supported Resolutions Resolutions up to 1280 x 1024 @ 60Hz

Aspect Ratio 5:4

Response Time 5ms

Contrast Ratio 1000:1

Brightness 250 cd/m

Color Depth 8-bit, 16.7M colors

Pixel Pitch Support 0.264 x 0.264 mm

Viewing Angle 170 (H), 160 (V)

Maximum Number of Users 1

MTBF 50, 000 Hrs

Connector(s)

Host Connectors 1 - VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note The minimum mounting depth of this rackmount console (17.7in / 45.0cm) is less than the length of the console itself (18.5in / 47.1cm). Please consider the length of the rackmount console when evaluating if it will fit into your rack.

Indicators

LED Indicators 1 - Power / Status LED

Power

Power Source	International Power Cords
Input Voltage	100 - 240 AC
Input Current	1.5A
Power Consumption (In Watts)	13W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10 ~ 80% RH (non-condensing)

Physical Characteristics

Color	Black
Material	Steel
Cable Length	6ft
Product Length	18.5 in [47.1 cm]
Product Width	17.6 in [44.8 cm]
Product Height	1.7 in [4.2 cm]
Weight of Product	25.6 lb [11.6 kg]
Maximum Mounting Depth	31.1 in [79 cm]
Minimum Mounting Depth	17.7 in [45 cm]

Packaging Information

Package Quantity	1
Package Length	24.6 in [62.4 cm]
Package Width	30.7 in [78.1 cm]
Package Height	7.7 in [19.6 cm]
Shipping (Package) Weight	38.1 lb [17.3 kg]

What's in the Box

Included in Package	1 - KVM console
	1 - KVM cable
	8 - M5 cage nuts
	8 - M5 screws
	5 - regional power cords (NA, JP, UK, EU, ANZ)
	2 - mounting rails
	1 - quick-start guide

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

