

Rackmount KVM Console HD 1080p - Single Port VGA KVM with 17" LCD Monitor for Server Rack - Fully Featured 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

Product ID: RKCONS17HD



Providing centralized control of your single PC or dozens of servers, this HD rackmount KVM console (QWERTY keyboard) also gives you easy access to and visibility of your system while it's mounted in a server rack or cabinet. Connected to your servers through a separate KVM switch (sold separately), the LCD console installs into 1U of rack-space, offering a space-efficient solution for complete console control.

The 1080p KVM console's monitor is 17.3" and LED back-lit, for low power consumption. It supports high-definition resolutions up to 1920x1080 providing sharper video performance. This HD console also provides more screen space, helping you to run multiple applications on the same screen, increasing your productivity.

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rackmount VGA KVM features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

This single-port KVM console comes with everything you need to set up:

- 1 Audio Cable
- 1 Set of KVM Cables (VGA)
- 2 Rear Mounting Brackets
- M5 Cage Nuts and Screws

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard and a touchpad for intuitive control, as well as a high-definition LCD display.

StarTech.com offers a wide selection of KVM consoles to help you access your systems more efficiently without the expense and clutter of extra peripherals. This rackmount KVM console is backed by a 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Large server farms
- Colocation facilities

Features

- **HIGH DEFINITION:** Rackmount KVM console w/high-resolution widescreen (16:9) 1080p LCD panel is perfect for applications needing extra detail or substantial info on one screen E.g. IP camera monitoring
- **WIDE COMPATIBILITY:** This HD KVM console drawer works with virtually any KVM switch brand or model that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- **VERSATILE INTERFACES:** Rack mount monitor with 17.3" Active Matrix TFT 16:9 widescreen 1U height Single Port Full keyboard + Trackpad Integrated Power Supply Supports VGA + USB
- **MAX DURABILITY:** Features durable steel housing and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 44,230 hour MTBF with 24/5 Tech Support
- **TESTED AND PROVEN:** Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product

Hardware

Warranty	2 Years
U Height	1U
Audio	No
Display Size	17.3"
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB
PC Video Type	VGA

Number of Monitors Supported 1

Rack-Mountable Yes

Cables Included Yes

Performance

On-Screen Display Yes

IP Control No

Maximum Analog Resolutions 1920x1080

Supported Resolutions Resolutions up to 1920x1080 @ 60Hz

Aspect Ratio 16:9

Contrast Ratio 800:1

Brightness 300 cd/m

Color Depth 6-bit, 262144 colors

Pixel Pitch Support 0.1989 x 0.1989 mm

Viewing Angle 170 (H), 170 (V)

Maximum Number of Users 1

MTBF 44,230 hours

Connector(s)

Host Connectors 1 - HD15 (15 pin, High Density D-Sub)

Other Interface(s) 1 - IEC 60320 C14 Power

Special Notes / Requirements

Note The minimum mounting depth of this rackmount console is less than the length of the console itself. Please consider the length of the rackmount console when evaluating if it will fit into your rack.

Indicators

LED Indicators 1 - Power / Status LED

Power

Power Source	International Power Cords
Input Voltage	100 - 240 AC
Input Current	1.5A
Power Consumption (In Watts)	13W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10 ~ 80% RH

Physical Characteristics

Color	Black
Material	Steel
Cable Length	1.8 m
Product Length	22.2 in [56.5 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.3 cm]
Weight of Product	24.7 lb [11.2 kg]
Maximum Mounting Depth	33.5 in [85 cm]
Minimum Mounting Depth	20.1 in [51 cm]

Packaging Information

Package Quantity	1
Package Length	24.3 in [61.6 cm]
Package Width	30.7 in [78.0 cm]
Package Height	7.5 in [19.1 cm]
Shipping (Package) Weight	36.0 lb [16.3 kg]

What's in the Box

Included in Package	1 - KVM console
	1 - KVM cable
	8 - M5 cage nuts
	8 - M5 screws
	5 - regional power cords (NA, JP, UK, EU, ANZ)
	1 - quick-start guide
	2 - mounting rails

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

