

Rackmount KVM Console - Single Port VGA KVM with 19" LCD Monitor for Server Rack - Fully Featured Universal 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

Product ID: RKCONS1901



This rack-mount KVM console provides complete keyboard, monitor and mouse control for a single server or multiple servers, connected through a separate KVM switch (sold separately). The 19 in. console installs into 1U of rack space, offering a space-efficient solution for complete console control.

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard (QWERTY) and a touchpad for intuitive control, as well as an LCD display that supports resolutions up to 1280x1024.

This versatile LCD console has a 19 in. screen. The increased screen space allows you to run multiple applications on the same screen, increasing your productivity.

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rack-mount VGA console features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

The rack console features a single-port KVM module, which enables you to connect it directly to a server. The module offers the flexibility you need to easily integrate it into your existing server infrastructure.

The RKCONS1901 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

Features

- **FLEXIBLE DESIGN:** This rackmount KVM console drawer works with all KVM switch brands and models that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- **VERSATILE INTERFACES:** Rack mount monitor w/ 19" Active Matrix TFT 1280 x 1024 LCD 1U height 99 key full keyboard with numeric keypad + Trackpad Supports VGA and USB Integrated Power Supply
- **MAX DURABILITY:** Features durable steel housing design and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 50,000 hour MTBF
- **TESTED AND PROVEN:** Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product
- **KVM Collection:** Can be purchased with integrated 8-port (RKCONS1908K) or 16-port (RKCONS1916K) KVM or use with StarTech.com enterprise KVM switches: SV831DUSB, SV831DUSBUK, SV1631DUSBU, SV1631DUSBUK

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	No
Audio	No
Display Size	19"
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Cables Included	Yes

Performance

On-Screen Display	Yes
IP Control	No
Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1280 x 1024
	Lower resolutions are also supported
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.264 x 0.264 mm
Maximum Number of Users	1
MTBF	50, 000 Hrs

Connector(s)

Console Interface(s)	1 - VGA (15 pin, High Density D-Sub)
----------------------	--------------------------------------

Indicators

LED Indicators	1 - power / status LED
----------------	------------------------

Power

Power Source	International Power Cords
Input Voltage	100 - 240 AC
Output Voltage	100-200 AC
Power Consumption (In Watts)	17W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
-----------------------	-------------------------

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 10 ~ 80% RH

Physical Characteristics

Color	Black
Material	Steel
Cable Length	6.0 ft [1.8 m]
Product Length	21.5 in [54.5 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.3 cm]
Weight of Product	26.9 lb [12.2 kg]
Maximum Mounting Depth	30.7 in [78 cm]
Minimum Mounting Depth	19.7 in [50 cm]

Packaging Information

Package Quantity	1
Package Length	24.4 in [61.9 cm]
Package Width	30.7 in [78.1 cm]
Package Height	7.5 in [19.0 cm]
Shipping (Package) Weight	42.5 lb [19.3 kg]

What's in the Box

Included in Package	1 - KVM console
	1 - 6 ft [1.8 m] KVM cable
	8 - M5 cage nuts
	8 - M5 screws
	5 - regional power cords (NA, JP, UK, EU, ANZ)
	2 - mounting rails (variable length)

1 - quick-start guide

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

