

8 Port Rackmount KVM Console w/ 6ft Cables - Integrated KVM Switch w/ 19" LCD Monitor - Fully Featured 1U LCD KVM Drawer- OSD KVM - Durable 50,000 MTBF - USB + VGA Support

Product ID: RKCONS1908K



This rack-mount KVM console provides complete keyboard, monitor and mouse control for eight computers. The rack-mount console installs into 1U of rack space, offering a space-efficient solution for complete console control.

This 8-port KVM switch provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in touchpad, keyboard (QWERTY) for intuitive control and an LCD display that supports resolutions up to 1280x1024.

This versatile rack-mount LCD console has a 19 in. screen. The increased screen space allows you to run multiple applications on the same screen, increasing your productivity.

The console slides out from 1U of rack space, enabling you to easily monitor and control eight servers and even more if connecting through a KVM switch. The rackmount VGA console features a handle for easy sliding in and out of the server rack, keeping your area organized and clutter-free.

The rackmount LCD features an 8-port KVM module, which enables you to connect it directly to eight servers. The KVM module offers the flexibility you need for easily integrating the console into your existing server infrastructure.

The RKCONS1908K is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

Features

- TECH SPECIFICATIONS: Rackmount KVM Console, 19" Active Matrix TFT LCD Monitor, 1280 x 1024, 8 port VGA KVM switch w/ 6 ft. cables, 99 key full keyboard + numeric keypad & trackpad; Supports USB 2.0
- PROFESSIONAL & SECURE: Customizable hot-keys, on-screen display (OSD), multi-level user security, user access levels / port permissions, & auto scan
- INTEGRATED DESIGN: Combines a KVM + Console w/ integrated power supply into 1U of rack space allowing space for other equipment. Mount depth: 23.8" [60.5 cm] to 35" [89 cm] (incl. mounting hardware)
- HEAVY DUTY: LCD KVM drawer has durable steel construction and heavy duty rail design that supports frequent use in operating environments from 0C to 40C (32F to 104F) with an MTBF of 50,000 hours
- TESTED & PROVEN: This OS independent rack console is universally compatible w/ leading servers and backed by a StarTech.com 2-year warranty and free lifetime 24/5 multilingual technical support

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	No
Audio	No
Display Size	19"
Panel Type	Active Matrix TFT LCD
KVM Ports	8
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Cables Included	Yes

Daisy-Chain	No
<hr/>	
Performance	
On-Screen Display	Yes
IP Control	No
Maximum Analog Resolutions	1280 x 1024
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1280 x 1024
Lower resolutions are also supported	
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	8-bit, 16.7M colors
Pixel Pitch Support	0.264 x 0.264 mm
Maximum Number of Users	1
MTBF	50, 000 Hrs
<hr/>	
Connector(s)	
Console Interface(s)	8 - VGA (15 pin, High Density D-Sub)
Host Connectors	1 - VGA (15 pin, High Density D-Sub)
Other Interface(s)	1 - VGA (15 pin, High Density D-Sub) 2 - USB 2.0 Type-A (4 pin, 480Mbps)
<hr/>	
Power	
Power Source	International Power Cords
Input Voltage	100 - 240 AC
Input Current	1.5A
Output Voltage	100-200 AC

Power Consumption (In Watts) 21W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10 ~ 80% RH

Physical Characteristics

Color	Black
Material	Steel
Product Length	25.3 in [64.3 cm]
Product Width	19.0 in [48.3 cm]
Product Height	1.7 in [4.3 cm]
Weight of Product	29.5 lb [13.4 kg]
Maximum Mounting Depth	35.0 in [89 cm]
Minimum Mounting Depth	23.8 in [60.5 cm]

Packaging Information

Package Quantity	1
Package Length	24.6 in [62.4 cm]
Package Width	30.5 in [77.5 cm]
Package Height	7.4 in [18.9 cm]
Shipping (Package) Weight	44.9 lb [20.4 kg]

What's in the Box

Included in Package	1 - Rack Console
	8 - 6 ft [1.8 m] KVM cables
	8 - M5 cage nuts
	8 - M5 screws

5 - Regional Power Cords (NA, JP, UK, EU, ANZ)

4 - Mounting Rails (variable lengths)

1 - Quick-Start Guide

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

