

6 ft. (1.8 m) USB KVM Cable for StarTech.com Rackmount Consoles

Product ID: RKCONSUV6



This 6 ft. (1.8 m) USB KVM Cable enables your StarTech.com Rackmount LCD console and KVM switch kit to conveniently operate your VGA and USB-equipped server.

This line of KVM cables are available in variable lengths, and are the only cables engineered for guaranteed compatibility with the StarTech.com line of RKCONS series of Rackmount Consoles and KVM switches. Supported models of Rackmount LCD Consoles are: RKCONS1701, RKCONS17HD, RKCONS1708K, RKCONS1716K, RKCONS1901, RKCONS1908K, RKCONS1916K.

This KVM cable has been specifically designed for the StarTech.com line of Rackmount KVM and Console kit. The USB and VGA KVM cord is wired with a unique schematic that enables a single connector on the KVM to interface with both VGA and USB on your server. This space-saving design dramatically reduces cable-clutter in your server rack, and ensures a tidy, professional server room.

When connected to an HD rackmount console, the 6-foot KVM cable supports HD resolutions up to 1920x1200 including 1080p, maintaining the quality of your server's video card to deliver every detail in high-definition.

To support the complexities and demands of your data center, this 6 foot (1.8 meter) KVM cable is also available as a 10 foot 3 meter KVM Cable (RKCONSUV10), and a 15 foot (4.6 meter) KVM cable (RKCONSUV15).

The RKCONSUV6 is backed by a StarTech.com Lifetime warranty and free technical support.

Certifications, Reports and Compatibility



Applications

- Connect servers to your StarTech.com Rackmount KVM console
- Keep replacement cables on hand to ensure continuous control of your mission critical servers

Features

- Maintain your clutter-free server room with a VGA and USB KVM cable that combines into a single connector on the KVM side
- Get crystal-clear picture quality with support for HD resolutions up to 1920x1200 or 1080p
- Accommodate variable rack configurations, with cables available in different lengths

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (14 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.2 in [3.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	8.4 oz [238.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	7.0 in [17.7 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.3 in [3.4 cm]
Shipping (Package) Weight	8.5 oz [240.0 g]

What's in the Box

Included in Package	1 - KVM Cable
---------------------	---------------

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

