

10 Outlet Rack Mount Power Strip 125V/16 Amp - 1U Horizontal 19" Rackmount PDU - NEMA 5-20P Input - 10x NEMA 5-15/20R Outlets - Rack Mount PDU - UL Listed - 8ft Power Cord

Product ID: RKPW101920



This 10-outlet (125V 16A) Rack PDU delivers a power distribution solution for your server rack/cabinet. The business-grade 1U power distribution unit can be mounted horizontally in any 19 inch server rack 4" in depth or greater, to provide ten 125V (16A) power outlets. You can access ten plugs on the front of the horizontal-mount network rack PDU.

Consolidate Power Sources

This power distribution system consolidates your power source and enables you to control all powered devices from one switch. The front of the rackmount power strip features two LEDs that indicate proper ground and surge detection, while enabling you to control the power state with an illuminated power/reset switch. This PDU includes an 8 ft long power cord.

Built to Last

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in 20 Amp (20A) circuit breaker and reset switch, ensuring dependable performance of vital equipment. To ensure maximum durability, the power distribution unit itself features a rugged steel casing.

This RKPW101920 rack mount power strip is backed by a 2-year StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

Features

- **10 OUTLET RACK MOUNT POWER STRIP:** 10x 5-15/20R Outlets; 16 Amps; Max Input & Output: 125V; 8ft. NEMA 5-20P Power Cord; UL Listed PDU; For 19" Racks/Cabinets; Front-Facing Power Switch; Horizontal Mount
- **20 AMP CIRCUIT BREAKER:** This 10 outlet rackmount power strip features a built-in 20A circuit breaker, with included 8 ft long NEMA 5-20P to IEC 60320 C19 power cord
- **EASY INSTALLATION:** The rack-mount PDU with metal housing supports 19 inch rack 1U horizontal installation, and meets ANSI/EIA RS-310-D standards
- **BROAD COMPATIBILITY:** 1U horizontal rack-mounted power distribution unit fits many network / data 2-post and 4-post racks; Compatible with 19" server racks with minimum 4" (10.2cm) depth
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this rack mountable power bar is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
U Height	1U
Form Factor	Horizontal
Number of Power Outlets	10
Rack-Mountable	Yes

Performance

Maximum Total Current	20A
Maximum Total Current Draw per Phase	20A
Regulatory Derated Input Current (North America)	16A
Nominal Input Voltage	125V
Nominal Output Voltage	125V
Maximum Output Voltage	125V
Load Capacity	2500VA

Connector(s)

Input Connector(s)	1 - IEC 60320 C20 Power
--------------------	-------------------------

Output Connectors	10 - NEMA 5-20R (North America)
	1 - IEC 60320 C19 Power

Power

Input Voltage Frequency	50/60Hz
Input Voltage	125V (max.)
Input Current	16A (max.)
Output Voltage	125V (max.)
Output Current	16A (max.)
Plug Type	NEMA 5-20P

Environmental

Operating Temperature	0C to 40C
Storage Temperature	-10C to 60C
Humidity	5% (0C) to 95% (40C)

Physical Characteristics

Color	Black
Material	Aluminum
Cable Length	7.9 ft [2.4 m]
Product Length	5.1 in [13.0 cm]
Product Width	17.5 in [44.5 cm]
Product Height	2.0 in [5.0 cm]
Weight of Product	2.6 lb [1.2 kg]

Packaging Information

Package Quantity	1
Package Length	6.5 in [16.5 cm]
Package Width	23.1 in [58.7 cm]

Package Height 4.2 in [10.6 cm]

Shipping (Package) Weight 3.4 lb [1.5 kg]

What's in the Box

Included in Package	1 - Rackmount 10 Outlet Rackmountable Power Strip
	1 - 8 ft NEMA 5-20P to IEC 60320 C19 Power Cord
	1 - Quick-Start Guide

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***