

Server Rack PDU with 24 outlets - 0U

**Product ID:** RKPW247015



This 24 outlet rackmount power strip provides a 0U solution for your rackmount equipment and fits most 42U racks and equipment cabinets. The 10ft power cord provides plenty of reach to power outlets, and the 24 evenly spaced outlets help keep power cabling clean and efficiently routed.

## Certifications, Reports and Compatibility



## Applications

## Features

- Provides 24 (120V 15A) power outlets
- Mounts vertically, taking up 0U of rack space
- 10 ft (3 m) power cord

---

### Hardware

Warranty	Lifetime
Form Factor	Vertical

Number of Power Outlets 24

Rack-Mountable Yes

#### Performance

Maximum Total Current 15A

Maximum Total Current Draw per Phase 15A

Regulatory Derated Input Current (North America) 12A

Nominal Input Voltage 120V

Nominal Output Voltage 120V

Maximum Output Voltage 125V

#### Connector(s)

Input Connector(s) 1 - NEMA 5-15 Power (North America)

Output Connectors 24 - NEMA 5-15 Power (North America)

#### Power

Input Voltage 120 AC

#### Physical Characteristics

Color Black

Material Aluminum

Cable Length 10.0 ft [3.0 m]

Product Length 72.2 in [1835 mm]

Product Width 1.6 in [4.1 cm]

Product Height 1.6 in [4.0 cm]

Weight of Product 4.3 lb [2.0 kg]

#### Packaging Information

Package Quantity 1

Package Length 6.2 ft [1.9 m]

---

Package Width	3.1 in [8.0 cm]
Package Height	2.4 in [6.2 cm]
Shipping (Package) Weight	5.5 lb [2.5 kg]

---

#### What's in the Box

Included in Package	1 - 24 Outlet PDU
	1 - Mounting Bracket
	1 - Backing Plate
	1 - Bag of Screws

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

