

Juniper RX-70KM-SFP Compatible SFP Module - 1000BASE-ZX - 1GbE Single Mode Fiber SMF  
Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 70km - 1550nm - DDM

**Product ID:** RX70KMSFPST



The RX70KMSFPST is a Juniper RX-FXSM-SFP compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-ZX compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1550nm
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 70 km (43.5 mi)
- MTBF: 53,972,659 hours
- Power Consumption: Low power consumption
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

### Features

- 100% JUNIPER RX-70KM-SFP COMPATIBLE SFP TRANSCEIVER: Designed, programmed and tested to work with compatible Juniper switches and routers to deliver reliable 1GbE connectivity
- TECHNICAL SPECS: 1000BASE-ZX 1Gbps Single Mode (SMF) LC Connector 1550nm Digital Diagnostic Monitoring (DDM) Distances up to 70km (43.5mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Juniper routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Juniper
Industry Standards	IEEE 802.3z 1000BASE-ZX

---

### Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	70 km (43.5 mi)
Type	Single Mode
Wavelength	1550nm
Fiber Operating Mode	Full-Duplex
DDM	Yes

Compatible Networks 1000 Mbps (1 Gbps)

MTBF 53,972,659 hours

**Connector(s)**

Connector A 1 - SFP Slot

Connector B 1 - Fiber Optic LC Duplex

**Physical Characteristics**

Product Length 2.6 in [65.0 mm]

Product Width 0.6 in [1.4 cm]

Product Height 0.5 in [1.2 cm]

Weight of Product 2.5 oz [72.0 g]

**Packaging Information**

Package Length 4.5 in [11.4 cm]

Package Width 3.7 in [9.4 cm]

Package Height 1.3 in [3.2 cm]

Shipping (Package) Weight 1.7 oz [48.0 g]

**What's in the Box**

Included in Package 1 - SFP Transceiver

**Warranty Information**

Warranty Lifetime

*\*Product appearance and specifications are subject to change without notice.*