

## 10 ft Cat5e Blue Snagless Shielded RJ45 STP Cat 5e Patch Cable - 10ft Patch Cord

**Product ID:** S45PATCH10BL



StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cables offer reliable Ethernet connections. This 10ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To reduce susceptibility to EMI/RFI and near end cross-talk, the patch cable is shielded throughout the length of the cable, as well as around the RJ45 connectors. Our Cat5e Shielded F/UTP Snagless Patch Cables also feature a snagless design that protects the RJ45 clip from snagging during installation, as well as PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage.

StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cable is constructed of top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and backed by our Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Designed for Network Adapters, Hubs, Switches, Routers, DSL/Cable Modems and other applications requiring high-speed cables
- Works with 1000 BASE-T, 100 BASE-T, 10 BASE-T, Token Ring, ATM & ISDN networks
- Suited for all industrial applications

## Features

- StarTech.com Category 5e shielded cables are manufactured to meet or exceed CAT5e specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

---

### Hardware

Warranty	Lifetime
Number of Conductors	4-Pair STP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Shielded Snag-less

---

### Connector(s)

Connector A	1 - RJ-45
Connector B	1 - RJ-45

---

### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0-95% RH

---

### Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	4.3 oz [121 g]

---

### Packaging Information

Package Quantity	1
------------------	---

---

Package Length	6.8 in [17.3 cm]
Package Width	7.8 in [19.8 cm]
Package Height	1.1 in [2.9 cm]
Shipping (Package) Weight	4.8 oz [136.0 g]

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

