

25 ft Cat5e Blue Snagless Shielded RJ45 STP Cat 5e Patch Cable - 25ft Patch Cord

Product ID: S45PATCH25BL



StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cables offer reliable Ethernet connections. This 25ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To reduce susceptibility to EMI/RFI and near end cross-talk, the patch cable is shielded throughout the length of the cable, as well as around the RJ45 connectors. Our Cat5e Shielded F/UTP Snagless Patch Cables also feature a snagless design that protects the RJ45 clip from snagging during installation, as well as PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage.

StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cable is constructed of top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Designed for Network Adapters, Hubs, Switches, Routers, DSL/Cable Modems and other applications requiring high-speed cables
- Works with 1000 BASE-T, 100 BASE-T, 10 BASE-T, Token Ring, ATM & ISDN networks
- Suited for industrial applications

Features

- StarTech.com Category 5e shielded cables are manufactured to meet or exceed CAT5e specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

Hardware

| | |
|-----------------------|-----------------------------|
| Warranty | Lifetime |
| Number of Conductors | 4-Pair STP |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Fire Rating | CMG Rated (General Purpose) |
| Cable Type | Shielded Snag-less |

Connector(s)

| | |
|-------------|-----------|
| Connector A | 1 - RJ-45 |
| Connector B | 1 - RJ-45 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | -20C to 70C (-4F to 158F) |
| Humidity | 0-95% RH |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Blue |
| Wire Gauge | 24 AWG |
| Cable Length | 25.0 ft [7.6 m] |
| Product Length | 25.0 ft [7.6 m] |
| Weight of Product | 10.4 oz [296 g] |

Packaging Information

| | |
|------------------|---|
| Package Quantity | 1 |
|------------------|---|

| | |
|---------------------------|-------------------|
| Package Length | 7.1 in [18.1 cm] |
| Package Width | 7.8 in [19.8 cm] |
| Package Height | 1.6 in [4.0 cm] |
| Shipping (Package) Weight | 11.0 oz [312.0 g] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - 25 ft Blue Shielded Snagless Cat5e Patch Cable |
|---------------------|--|

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*