

Dual-Bay USB 3.0 to SATA Hard Drive Docking Station, USB Hard Drive Dock, External 2.5/3.5" SATA I/II/III SSD/HDD Docking Station, Hot-Swap Hard Drive Bay, Top-Loading

Product ID: SDOCK2U33



Our SDOCK2U33 Dual-Bay USB 3.0 to SATA Hard Drive Docking Station enables access to two 2.5/3.5" SATA drives from your desktop or laptop computer over USB 3.2 Gen 1 (5 Gbps).

The hard drive dock features power buttons for each individual drive, ensuring you can operate each hard drive separately. This gives you the freedom to hot-swap an idle drive while transferring data to another, saving you time.

Extend the value of this hard drive docking station further with the addition of our SATA to IDE Hard Drive Adapter (SAT2IDEADP), allowing easy insertion of any 2.5 or 3.5in. IDE hard drive into a SATA hard drive dock.

Compatible with Any Capacity or File Format

Compatible with 2.5" and/or 3.5" SATA HDDs and SSDs of any capacity and file format recognized by your host system. This dock works with any Operating System. Drivers and software are not required.

SDOCK2U33 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- System builders and I.T. specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Transferring data from one hard drive to another
- Technicians who test or benchmark multiple hard drives
- Backup important data and easily take the drive to an offsite location for safekeeping

Features

- HARD DRIVE DOCKING STATION: This 2-bay hard drive dock delivers instant access to your 2.5/3.5" SATA hard drives for file backup, disk imaging, or data transfer over USB 3.2 Gen 1 (5 Gbps). Tool-less design enables easy drive hot-swapping.
- DRIVE COMPATIBILITY: Supports 2.5/3.5" SATA HDDs & SSDs of any capacity OS Independent Backwards compatible w/ SATA I/II IDE adapter (SAT2IDEADP) sold separately Includes 3ft USB-A cable and universal power adapter
- PERFORMANCE: Independent power buttons for each bay enables you to hot-swap an idle drive while the other bay is in use. Drive bays with 15,000-cycle insertion rating for maximum durability.
- SPECS: 2-Bay Hard Drive Dock SATA I/II/III USB 3.2 Gen 1 (5 Gbps) Host Connection Tool-less/Tray-less Design Hot-Swappable Drive Bays Top-Loading/Toaster-Style with Eject Buttons LED Activity Lights
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this Dual-Bay Hard Drive Dock is backed for 2 years, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 3.2 Gen 1 (5Gbps)
Number of Drives	2
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA
Drive Installation	Removable
Chipset ID	VIA/VLI - VL817
	ASMedia - ASM225CM

Performance

UASP Support	Yes
Insertion Rating	15,000 Cycles
MTBF	30,000

Connector(s)

Drive Connectors	2 - SATA Data & Power Combo (7+15 pin)
Host Connectors	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	2 - Drive Power / Activity
----------------	----------------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.3 A
Output Voltage	12V DC
Output Current	3 A
Plug Type	M
Power Consumption (In Watts)	36

Environmental

Operating Temperature	5C to 35C (41F to 95F)
Storage Temperature	-20C to 50C (-4F to 122F)
Humidity	20%RH~80%RH

Physical Characteristics

Color	Black
Material	Plastic

Product Length	5.8 in [14.8 cm]
Product Width	5.2 in [13.2 cm]
Product Height	2.8 in [7.0 cm]
Weight of Product	1.1 lb [0.5 kg]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.9 cm]
Package Width	8.3 in [21.2 cm]
Package Height	4.8 in [12.2 cm]
Shipping (Package) Weight	2.1 lb [0.9 kg]

What's in the Box

Included in Package	1 - USB 3.0 to Dual 2.5/3.5in SATA hard drive docking station 1 - 3ft (1m) USB 3.0 Cable 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand 1 - Instruction Manual
---------------------	--

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***