

MSA Uncoded SFP Module - 100BASE-FX - 100MbE Multi Mode Fiber (MMF) Optic Transceiver - 100Mb Ethernet SFP - LC 2km - 1310nm - DDM

Product ID: SFP100BFXST



The SFP100BFXST is an MSA compliant fiber SFP transceiver that's designed, programmed and tested to work with 100BASE-FX compatible MSA switches and routers. The SFP transceiver module supports a maximum distance of up to 2 km (1.2 mi) and delivers dependable 100 Mb Ethernet connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 155 Mbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 2 km (1.2 mi)
- Power Consumption: Less than 1 Watt
- DDM: Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replace defective or damaged SFP modules
- Expand your network to remote segments

Features

- 100% MSA UNCODED SFP TRANSCEIVER: Designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver reliable 100MbE connectivity
- TECHNICAL SPECS: 100BASE-FX 100Mbps Multi Mode (MMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 2km (1.2mi)
- TESTED FOR COMPATIBILITY: Hot-swappable in MSA Compliant routers and switches; DDM support reports the transceiver's status to most SNMP network management tools.
- WORKS WITH MSA COMPLIANT SWITCHES: Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
WDM	No
Industry Standards	IEEE 802.3u 100BASE-FX

Performance

Maximum Data Transfer Rate	155 Mbps
Max Transfer Distance	2 km (1.2 mi)
Type	Multi Mode
Wavelength	1310nm
Fiber Operating Mode	Half/Full-Duplex

DDM	Yes
Compatible Networks	100 Mbps
Power Consumption (In Watts)	< 1 W

Connector(s)

Local Unit Connectors	1 - Fiber Optic LC Duplex
-----------------------	---------------------------

Special Notes / Requirements

Note	For use in 100 Mbps fiber networking equipment and media converters
------	---

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

Physical Characteristics

Color	Silver
Product Length	2.3 in [5.8 cm]
Product Width	0.5 in [1.4 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	0.7 oz [20.0 g]

Packaging Information

Package Length	3.7 in [9.3 cm]
Package Width	4.4 in [11.3 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	1.5 oz [42.0 g]

What's in the Box

Included in Package	1 - SFP transceiver
---------------------	---------------------

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

