

Dell EMC SFP-1G-BX80-D Compatible SFP Module - 1000BASE-BX-D - 1 GbE Gigabit Ethernet BiDi Fiber (SMF)

Product ID: SFP1GBX80DES



The SFP1GBX80DES is a Dell EMC SFP-1G-BX80-D compatible downstream fiber SFP transceiver which pairs with StarTech.com's SFP1GBX80UES. They are designed, programmed and tested to work with 1000BASE-BX80 compatible Dell EMC switches and routers. The SFP transceiver module supports a maximum distance of up to 80 km (49.7 mi) and delivers dependable 1 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1550nmTX/1490nmRX
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 80 km (49.7 mi)
- Power Consumption: Low power consumption
- DDM: Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- **100% DELL EMC SFP-1G-BX80-D COMPATIBLE:** 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Dell EMC switches and routers to deliver reliable 1GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 1 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 1000BASE-BX-D 1Gbps 1G Bi-Directional Downstream Single Mode (SMF) LC Connector 1550nmTX/1490nmRX Digital Diagnostic Monitoring (DDM) Distances up to 80km (49.7mi)
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Dell EMC routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Compatible Brand	Dell EMC
Industry Standards	IEEE 802.3 1000BASE-BX80

Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	80 km (49.7 mi)
Type	Single Mode
Wavelength	1550nmTX/1490nmRX
Fiber Operating Mode	Full-Duplex
DDM	Yes

Compatible Networks 1000 Mbps (1 Gbps)

MTBF 3,713,222 hours

Physical Characteristics

Product Length 0.5 in [1.4 cm]

Product Width 2.3 in [5.8 cm]

Product Height 0.5 in [1.3 cm]

Weight of Product 1.1 oz [30 g]

Packaging Information

Package Length 4.4 in [11.2 cm]

Package Width 3.6 in [9.2 cm]

Package Height 1.3 in [3.2 cm]

Shipping (Package) Weight 1.8 oz [50 g]

What's in the Box

Included in Package 1 - SFP Transceiver

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*