

Juniper SFP-GE10KT13R14 Compatible SFP Module - 1000BASE-BX-U - 1 GbE Gigabit Ethernet BiDi Fiber (SMF)

Product ID: SFPGE10KT3R4



The SFPGE10KT3R4 is a Juniper SFP-GE10KT13R14 compatible fiber transceiver module that has been designed, programmed, and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-BX10-U compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nmTx/1490nmRx
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,713,222 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- 100% JUNIPER SFP-GE10KT13R14 COMPATIBLE: 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver reliable 1GbE connectivity
- INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE: This 1 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- TECHNICAL SPECS: 1000BASE-BX-U 1Gbps 1G Bi-Directional Upstream Single Mode (SMF) LC Connector 1310nmTx/1490nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- PROGRAMMED & TESTED FOR COMPATIBILITY: Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Compatible Brand	Juniper
Industry Standards	IEEE 802.3 1000BASE-BX10-U

Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nmTx/1490nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes

Compatible Networks 1000 Mbps (1 Gbps)

MTBF 3,713,222 hours

Power Consumption (In Watts) < 1.3W

Connector(s)

Connector A 1 - SFP Slot

Connector B 1 - Fiber Optic LC Simplex

Physical Characteristics

Product Length 2.6 in [65.0 mm]

Product Width 0.6 in [1.4 cm]

Product Height 0.5 in [1.2 cm]

Weight of Product 2.5 oz [72.0 g]

Packaging Information

Package Length 4.4 in [11.2 cm]

Package Width 3.7 in [9.4 cm]

Package Height 1.3 in [3.2 cm]

Shipping (Package) Weight 1.8 oz [50.0 g]

What's in the Box

Included in Package 1 - SFP Transceiver

Warranty Information

Warranty Lifetime

***Product appearance and specifications are subject to change without notice.**