

Juniper SFP-GE10KT13R15 Compatible SFP Module - 1000BASE-BX-U - 1GbE Gigabit Ethernet BiDi Fiber (SMF)

Product ID: SFPGE10KT3R5



The SFPGE10KT3R5 is a Juniper SFP-GE10KT3R5 compatible fiber transceiver module that has been designed, programmed, and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-BX10-U compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nmTx/1550nmRx
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,713,222 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- **100% JUNIPER SFP-GE10KT13R15 COMPATIBLE:** 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver reliable 1GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 1000BASE-BX-U 1Gbps 10G Bi-Directional Upstream Single Mode (SMF) LC Connector 1310nmTx/1550nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	3 Years
Compatible Brand	Juniper
Industry Standards	IEEE 802.3 1000BASE-BX10-U

Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nmTx/1550nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes

	Compatible Networks	1000 Mbps (1 Gbps)
	MTBF	3,713,222 hours
	Power Consumption (In Watts)	< 1.3W
Connector(s)		
	Connector A	1 - SFP Slot
	Connector B	1 - Fiber Optic LC Simplex
Physical Characteristics		
	Product Length	2.6 in [65.0 mm]
	Product Width	0.6 in [1.4 cm]
	Product Height	0.5 in [1.2 cm]
	Weight of Product	2.5 oz [72.0 g]
Packaging Information		
	Package Length	4.4 in [11.2 cm]
	Package Width	3.6 in [9.2 cm]
	Package Height	1.3 in [3.2 cm]
	Shipping (Package) Weight	1.8 oz [50.0 g]
What's in the Box		
	Included in Package	1 - SFP Transceiver
Warranty Information		
	Warranty	3 Years

**Product appearance and specifications are subject to change without notice.*