

Cisco GLC-SX-MM Compatible SFP Module - 1000BASE-SX - 1GbE Multimode Fiber MMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 550m - 850nm - Cisco IE3400, IE3300, IE3200

**Product ID:** SFPGLCSXMMST



The SFPGLCSXMMST is a Cisco GLC-SX-MM compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1GbE (1000 Mbps) connectivity over fiber cable, for 1000BASE-SX compliant networks, with a maximum distance of up to 550 m (1804 ft).

#### Technical Specifications:

- Wavelength: 850 nm
- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 550 m (1804 ft)
- MTBF: 3,381,761 hours
- Power Consumption: Less than 1 Watt
- Digital Diagnostics Monitoring (DDM): No

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

## Features

- 100% CISCO GLC-SX-MM COMPATIBLE: Works with Cisco switches like IE3400, IE3300, IE3200, ME1200, ME2400 and others
- TECHNICAL SPECS: 1000BASE-SX 1 Gbps Multi Mode (MMF) LC Connector 850nm Distances up to 550m (1804ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
WDM	No
Industry Standards	IEEE 802.3z 1000BASE-SX

---

### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	550m [1804ft]
Type	Multi Mode
Wavelength	850nm

---

Fiber Operating Mode	Half/Full-Duplex
DDM	No
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,381,761 hours
Power Consumption (In Watts)	< 1 W

---

**Connector(s)**

Local Unit Connectors	1 - Fiber Optic LC Duplex
-----------------------	---------------------------

---

**Special Notes / Requirements**

Note	For use in Gigabit fiber networking equipment and media converters
------	--

---

**Power**

Output Voltage	3.3V DC
----------------	---------

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 85F)
Humidity	30~70% RH

---

**Physical Characteristics**

Color	Silver
Product Length	2.4 in [60.0 mm]
Product Width	0.5 in [1.2 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	0.6 oz [16.0 g]

---

**Packaging Information**

Package Length	4.4 in [11.2 cm]
Package Width	3.5 in [9.0 cm]

Package Height 1.3 in [3.3 cm]

Shipping (Package) Weight 1.7 oz [48.0 g]

---

**What's in the Box**

Included in Package 1 - 1.25 Gbps Multimode LC SFP

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

