

## 1 Port PCI Express PCIe Gigabit NIC Server Adapter Network Card - Low Profile

**Product ID:** ST1000SPEX2L



The ST1000SPEX2L Low-Profile PCIe Gigabit Network Card adds a 10/100/1000 Mbps compatible RJ45 Ethernet port to a PCI Express-enabled client, server or workstation, providing a convenient addition or replacement networking interface.

Compliant with IEEE 802.3/u/ab standards, and with support for 9K Jumbo Frames, VLAN tagging and Wake on LAN (WOL), this versatile Gigabit NIC/Server Adapter offers effective network performance.

The card comes pre-configured with a low-profile/half-height installation bracket and includes a standard profile bracket for installation in a wide range of computer/server chassis, regardless of form factor.

Backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Upgrade from 10/100 Ethernet capability to Gigabit capability
- Add an Ethernet port to a workstation or server computer, for redundancy or bridging

- Add networking capabilities to an old system with no Ethernet port

## Features

- A single 10/100/1000Mbps compatible RJ45 Ethernet port
- Gigabit detection and Link/Activity LED indicators
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3x and IEEE 802.3ab standards
- Supports IEEE 802.1Q VLAN tagging, IEEE 802.1P Layer 2 Priority Encoding and IEEE 802.3x Full Duplex Flow Control
- Jumbo frame support
- Full and half duplex support
- Supports Wake-on-LAN function
- Crossover Detection & Auto-Correction (Auto MDI/MDI-X)

---

### Hardware

Warranty	2 Years
Ports	1
Interface	RJ45 (Gigabit Ethernet)
Bus Type	PCI Express
Card Type	Low Profile (SP bracket incl.)
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3x, IEEE 802.3ab
Chipset ID	Realtek - RTL8111

---

### Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	1000 Mbps
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Jumbo Frame Support 9K max.

Supported Protocols CSMA/CD

#### Connector(s)

Connector Type(s) 1 - PCI Express x1

External Ports 1 - RJ-45

#### Software

OS Compatibility Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11

Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019

Mac OS X 10.6 to 10.9, Linux 2.4.x and up - LTS Versions only

#### Special Notes / Requirements

System and Cable Requirements Available PCI Express expansion card slot

#### Indicators

LED Indicators 1 - Gigabit Detect (Yellow)

1 - Link/Activity (Green)

#### Power

Input Voltage 12V DC

Output Voltage 12V DC

#### Environmental

Operating Temperature 0C to 70C (32F to 158F)

Storage Temperature 0C to 100C (32F to 212F)

Humidity 10% ~ 90% RH

#### Physical Characteristics

Color Black

Material Steel

Product Length 2.6 in [6.6 cm]

Product Width 1.7 in [4.2 cm]

Product Height 3.1 in [8.0 cm]

Weight of Product 1.1 oz [30.0 g]

---

**Packaging Information**

Package Quantity 1

Package Length 5.6 in [14.3 cm]

Package Width 5.6 in [14.3 cm]

Package Height 1.3 in [3.2 cm]

Shipping (Package) Weight 3.2 oz [92.0 g]

---

**What's in the Box**

Included in Package 1 - Gigabit Ethernet PCI Express Card

1 - Standard Profile Bracket

1 - Instruction Manual

---

**Warranty Information**

Warranty 2 Years

---

*\*Product appearance and specifications are subject to change without notice.*