

4-Port USB 3.0 Hub - 5Gbps - Metal Industrial USB-A Hub - Wall or Desk Mountable USB Data Hub  
- TAA Compliant USB Expander Hub

**Product ID:** ST4300USBM



This TAA compliant 4-port industrial USB 3.2 Gen 1 hub gives you the scalability you need in harsh industrial environments, product and repair labs, conference rooms or office workstations. With its rugged industrial grade metal housing, it is designed to meet the advanced requirements of connecting a high number of devices in factories and office environments.

This industrial USB hub delivers reliable performance with a metal, heavy-duty housing. It supports wide-range 7-24V DC terminal block input, giving you the flexibility to power the hub as required, based on your own power input capabilities.

Perfect for factory environments, the rugged hub also supports a wide operating temperature range (0C to 55C) and offers ESD protection to each USB port, which can help prevent damage to your connected devices.

Designed for a high volume of connections, this robust USB 3.2 Gen 1 hub offers four connection ports, for connecting more USB devices and peripherals.

The hub also supports USB battery charging specification 1.2, delivering up to 2.4A on any port to a maximum of 20W total, so you can charge your mobile devices faster than traditional USB ports allow.

With versatile installation options, you can install the hub where it's best suited for your environment. With built-in mounting brackets and an included 1.8-meter USB host cable, you can securely mount the USB 3.2 Gen 1 hub to most surfaces such as a wall, under a desk or rack.

StarTech.com offers an external power adapter, ITB20D3250, sold separately. The universal DC power adapter can be used as an alternative, back up or replacement power supply for StarTech.com's line of industrial USB hubs.

The rugged USB hub supports the full 5 Gbps bandwidth of USB 3.2 Gen 1 and is backward compatible with previous USB devices. You can connect your legacy peripherals alongside your newer USB 3.2 Gen 1 devices without any disruptions.

The ST4300USBM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Ideal for tough conditions that are subject to large temperature variances, or where there's a risk of physical damage
- Great for industrial and manufacturing environments where only terminal block connection is preferred
- Connect a variety of USB devices such as industrial printers or cameras, plus fast-charge your smartphone and tablet
- Mount to a wall near or under a desk surface in a Lab, Service Repair area or office area connecting multiple USB peripherals
- Use in a conference or meeting room utilizing multiple USB peripherals or for charging several mobile devices

## Features

- Protects your connected devices with 8kV Air and 4kV Contact ESD protection
- Mount industrial USB 3.2 Gen 1 hub where required with built-in mounting brackets
- Offers flexible, wide-range power inputs with a 7-24V DC terminal block
- USB Battery Charging Specification 1.2 up to 2.4A on any port to a maximum of 20W total
- Adds four USB 3.2 Gen 1 ports from a single USB connection

---

### Hardware

|                       |         |
|-----------------------|---------|
| Warranty              | 2 Years |
| USB-C Device Port(s)  | No      |
| USB-C Host Connection | No      |
| Fast-Charge Port(s)   | No      |

---

|            |                       |
|------------|-----------------------|
| Ports      | 4                     |
| Interface  | USB 3.2 Gen 1 (5Gbps) |
| Bus Type   | USB 3.2 Gen 1 (5Gbps) |
| Chipset ID | VIA/VLI - VL817       |

---

**Performance**

|                            |                                  |
|----------------------------|----------------------------------|
| Maximum Data Transfer Rate | 5 Gbps (USB 3.2 Gen 1)           |
| Type and Rate              | USB 3.2 Gen 1 - 5 Gbit/s         |
| ESD Protection             | +/-8kV (Air)<br>+/-4kV (Contact) |
| MTBF                       | 245,881 Hours                    |

---

**Connector(s)**

|                |   |
|----------------|---|
| External Ports | 1 - Terminal Block (2 Wire)<br><br>4 - USB Type-A (9 pin, 5 Gbps)<br><br>1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps) |
|----------------|---|

---

**Software**

|                  |  |
|------------------|--|
| OS Compatibility | OS Independent; No additional drivers or software required |
|------------------|--|

---

**Special Notes / Requirements**

|                               |                        |
|-------------------------------|------------------------|
| System and Cable Requirements | Available USB 3.0 port |
|-------------------------------|------------------------|

---

**Indicators**

|                |  |
|----------------|--|
| LED Indicators | 1 - Power (Red)<br><br>4 - USB Device Connection (Green) |
|----------------|--|

---

**Power**

|                |                     |
|----------------|---------------------|
| Power Source   | AC Adapter Included |
| Output Voltage | 12V DC              |
| Output Current | 3A                  |

Center Tip Polarity      Positive

Plug Type      M

Power Consumption (In  
Watts)      36

#### Environmental

Operating Temperature      0C to 55C (32F to 131F)

Storage Temperature      -20C to 85C (-4F to 185F)

Humidity      5~95% RH

#### Physical Characteristics

Color      Black

Form Factor      Industrial

Material      Steel

Product Length      7.0 in [17.9 cm]

Product Width      2.3 in [6.0 cm]

Product Height      0.9 in [2.4 cm]

Weight of Product      10.0 oz [282 g]

#### Packaging Information

Package Quantity      1

Package Length      7.5 in [19.0 cm]

Package Width      11.6 in [29.5 cm]

Package Height      2.8 in [7.2 cm]

Shipping (Package)  
Weight      2.6 lb [1.2 kg]

#### What's in the Box

Included in Package      1 - Industrial USB 3.0 Hub

1 - 6 ft [1.8 m] USB 3.0 cable (non-locking)

1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)

1 - Instruction Manual

1 - Terminal Block (2 Wire)

---

**Warranty  
Information**

|          |         |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

---

*\*Product appearance and specifications are subject to change without notice.*

