

2 Port DisplayPort KVM Switch - 4K 60Hz - Compact Dual Port UHD DP 1.2 USB Desktop KVM Switch with 4ft Cables & Audio - Bus Powered & Remote Switching - MacBook ThinkPad

Product ID: SV211DPUA4K



The SV211DPUA4K 2-Port 4K60Hz DisplayPort Cable KVM Switch with Audio and Remote Switching Control gives you control of two DisplayPort, USB equipped computers with a single monitor, keyboard, mouse and audio peripheral set.

The DisplayPort KVM switch supports resolutions up to 4K at 60Hz and can drive one large DP display with ease, maximizing viewing space. With support for separate 3.5 mm stereo audio, the KVM switch delivers full audio compatibility across connected computers.

This DP KVM switch is OS independent, meaning it can work with any USB-A and DisplayPort equipped desktop computer or laptop.

The switch features a remote push-button on a 1.5 meter (4ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and optional PC or Mac compatible software for switching between systems.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

The SV211DPUA4K is backed by a 2-year StarTech.com warranty and free lifetime multilingual technical support.

Certifications, Reports and Compatibility





Applications

Features

- **SPACE-SAVING DESIGN:** Compact 2 Port DisplayPort KVM Switch w/ built-in cables & remote switching provides USB powered control of two computers from one keyboard, monitor, and mouse
- **4K VIDEO QUALITY:** DP UHD KVM switch supports resolutions up to 4K at 60Hz on a single DisplayPort monitor for maximized viewing space
- **TECH SPECS:** Dual Port KVM DisplayPort 1.2 4K 60Hz 3840x2160 Hotkey, Integrated Remote Push Button, Software OS Independent Bus Powered Analog Audio Switching DisplayPort/USB Console
- **COMPACT & USER FRIENDLY:** 3 ways to switch between PCs (Dell, HP, Apple & Lenovo): Remote push-button, hotkeys, and manual switching; offers space saving design with minimal footprint
- **THE STARTECH.COM ADVANTAGE:** Desktop KVM switch comes with a 2-year StarTech.com warranty and free lifetime 24/5 multilingual technical support based in North America on this 2 port KVM switch

Hardware

| | |
|------------------------------|-------------|
| Warranty | 2 Years |
| Audio | Yes |
| KVM Ports | 2 |
| PC Interface | USB |
| PC Video Type | DisplayPort |
| Number of Monitors Supported | 1 |
| Rack-Mountable | No |
| Cables Included | Yes |
| Daisy-Chain | No |

Performance

| | |
|-------------------|-----------------|
| On-Screen Display | No |
| Video Revision | DisplayPort 1.2 |

| | |
|-----------------------------|------------------------------------|
| IP Control | No |
| Hot-Key Selection | Yes |
| Maximum Digital Resolutions | 3840 x 2160 (Ultra HD 4K) @ 60hz |
| Wide Screen Supported | Yes |
| Audio Specifications | Two Channel Audio Input and Output |
| Auto Scan | 10, 20, 30, 40, 50, and 60 seconds |
| Port Selection Support | Push Button, Hotkeys, and Software |
| MTBF | 1,012,884 hours |

Connector(s)

| | |
|----------------------|---|
| Console Interface(s) | 2 - USB 2.0 Type-A (4 pin, 480Mbps) 1 - DisplayPort (20 pin) 2 - 3.5 mm Mini-Jack (3 Position) Female |
| Host Connectors | 2 - USB 2.0 Type-A (4 pin, 480Mbps) 2 - DisplayPort (20 pin) 4 - 3.5 mm Mini-Jack (3 Position) Female |

Software

| | |
|------------------|--|
| OS Compatibility | Windows 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022 Mac OS 10.6 to 10.12 |
|------------------|--|

Special Notes / Requirements

| | |
|------|---|
| Note | In order to access the software and hotkeys of the KVMs, a compatible OS must be installed on the connected host, however the KVM and push button switching functions are OS independent. |
|------|---|

Indicators

| | |
|----------------|------------|
| LED Indicators | 2 - Orange |
|----------------|------------|

Power

Power Source Bus Powered

Input Voltage 5V DC

Output Voltage 5 DC

Environmental

Operating Temperature 0 ~ 40C

Storage Temperature -20 ~ 60C

Humidity 0 ~ 90% RH, Non-Condensing

**Physical
Characteristics**

Color Black

Material Plastic

Cable Length 4.0 ft [1.2 m]

Product Length 3.8 in [9.7 cm]

Product Width 3.2 in [8.2 cm]

Product Height 0.4 in [0.9 cm]

Weight of Product 15.5 oz [438.0 g]

**Packaging
Information**

Package Quantity 1

Package Length 9.8 in [25.0 cm]

Package Width 6.3 in [16.1 cm]

Package Height 2.6 in [6.5 cm]

Shipping (Package)
Weight 1.2 lb [0.5 kg]

What's in the Box

Included in Package 1 - KVM Switch

1 - Quick-Start Guide

**Warranty
Information**

Warranty

2 Years

**Product appearance and specifications are subject to change without notice.*

