

2 Port Dual Monitor HDMI KVM Switch - 4K 60Hz Ultra HD HDR - Desktop 4K HDMI 2.0 KVM Switch with 2 Port USB 3.0 Hub (5Gbps) & 4x USB 2.0 HID, Audio - Hotkey Switching - TAA

Product ID: SV231DHU34K6



This 2-port KVM switch combines 4K (60Hz) digital display capabilities with control of two connected computers.

The HDMI KVM switch supports resolutions up to 4K at 60Hz. It drives two large monitors at the full 4K resolution. Includes EDID and HDCP signal emulation so monitors always remain synced for faster switching times, and desktop settings are maintained to avoid disrupting your workflow.

With support for digital audio (with supporting displays and sources) and separate 3.5 mm stereo audio, the HDMI 2.0 KVM switch delivers full audio compatibility.

The integrated USB 3.0 hub shares two peripherals (in addition to keyboard and mouse) among attached computers as if they were directly connected to your host computer, eliminating the cost of duplicate devices such as printers and scanners.

While supporting Windows, this HDMI KVM switch is also compatible with Mac and Linux operating systems.

The front-panel pushbuttons make it easy to switch between systems and activate the auto-scan feature. The hotkey functionality makes accessing each system quickly, while a buzzer sound confirms the switch.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice, and monitors.

This 2-port HDMI KVM switch is backed by a 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

Features

- DUAL 4K 60Hz UHD: 2 Port HDMI Dual Screen KVM switch supports up to 4K at 60Hz on two monitors for applications like CAD/CAM, video editing and content creation; works with major brands including Dell, HP, and Lenovo
- FAST SWITCHING: Includes EDID and HDCP signal emulation so monitors stay synced for faster switching times, and desktop settings are maintained to avoid disrupting your workflow while switching between up to 2 computers
- TECH SPECS: 2-Port Dual Screen HDMI 2.0 3840 x 2160 HDCP 2.2 HDR10 Support 2 Port USB 3.0 Hub (5Gbps) 4x USB HID Hotkey, Push Buttons Stereo Analog + 7.1 Digital Audio EDID & HDCP Emulation OS Independent
- USER-FRIENDLY: KVM switch with compact & durable steel housing featuring easily accessible buttons & front-mounted integrated USB switch (USB 3.1/3.2 Gen 1) for sharing USB devices between connected computers
- STARTECH.COM ADVANTAGE: IT professionals' choice for over 30 years; This KVM (Keyboard, Video/Monitor, Mouse) Switch is backed for 2-years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB 3.2 Gen 1 (5Gbps)
PC Video Type	HDMI
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	No

Chipset ID Genesys Logic - GL3523

Daisy-Chain No

Performance

On-Screen Display No

Video Revision HDMI 2.0

IP Control No

Hot-Key Selection Yes

Maximum Data Transfer Rate 5Gbps

Supported Resolutions 3840 x 2160 @60Hz

Wide Screen Supported Yes

Audio Specifications HDMI - 7.1 Channel Audio
HDMI - 2 Channel Audio
Analog Stereo - 2 Channel Audio

Auto Scan 3, 8, 15 & 30 seconds

Maximum Number of Users 1

Port Selection Support Push Button and Hotkeys

MTBF 156 000 hrs

Connector(s)

Console Interface(s) 2 - 19 pin HDMI Female
1 - 3.5 mm Audio Female
2 - USB Type-A (9 pin, 5 Gbps)
4 - USB Type-A (4 pin; HID Port) USB 1.1

Host Connectors 2 - 9 pin USB 3.0 B Female
4 - 19 pin HDMI Female
2 - 3.5 mm Audio Female

Other Interface(s) 1 - USB Mini-B (5 pin)

Indicators

LED Indicators 2 - Green (Power/Sync)
2 - Red (Selected Host)

Power

Power Source AC Adapter Included
Input Voltage 100 - 240 AC
Input Current 1.0A
Output Voltage 12V DC
Output Current 3A
Center Tip Polarity Positive
Plug Type M
Power Consumption (In Watts) 36W

Environmental

Operating Temperature 0-40
Storage Temperature -10 to 60
Humidity 0% to 80%

Physical Characteristics

Color Black
Material Steel
Product Length 6.3 in [16.0 cm]
Product Width 3.9 in [10.0 cm]
Product Height 2.3 in [5.8 cm]
Weight of Product 1.8 lb [0.8 kg]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.9 cm]
Package Width	9.4 in [24.0 cm]
Package Height	3.8 in [9.6 cm]
Shipping (Package) Weight	2.9 lb [1.3 kg]

What's in the Box

Included in Package	1 - KVM Switch
	1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
	4 - Rubber Feet
	1 - Quick-Start Guide

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

