

4 Port Black USB KVM Switch Kit with Cables and Audio

Product ID: SV411KUSB



The SV411KUSB 4 Port USB KVM Switch Kit with Audio and Cables lets you control up to four USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes four, 4ft 4-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

Features

- Switching type: Hotkey, push-button
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Cables (4 ft.) included

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	4
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog	2048 x 1536 pixels

Resolutions	
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (15 pin, High Density D-Sub)
Host Connectors	8 - 3.5 mm Mini-Jack (3 Position)
	4 - VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0C ~ 40C (32F ~ 104F)
Storage Temperature	-20 ~ 60C (-4F ~ 140F)
Humidity	0 ~ 90% RH, Non-Condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	4.0 ft [1.2 m]
Product Length	2.4 in [61 mm]
Product Width	3.7 in [9.5 cm]
Product Height	1.0 in [2.5 cm]

Weight of Product 6.7 oz [189 g]

Packaging Information

Package Quantity 1

Package Length 8.1 in [20.7 cm]

Package Width 5.6 in [14.3 cm]

Package Height 7.0 in [17.7 cm]

Shipping (Package) Weight 3.0 lb [1.4 kg]

What's in the Box

Included in Package

- 1 - 4 Port KVM Switch
- 4 - 4ft. VGA USB KVM Cable
- 4 - 4ft. Audio Cable (3.5mm speaker/mic)
- 1 - Driver CD
- 1 - Instruction Manual

Warranty Information

Warranty 2 Years

****Product appearance and specifications are subject to change without notice.***