

USB Dual VGA over Cat5 KVM Console Extender - 650 ft / 200m - TAA

Product ID: SV565DUTPU



The SV565DUTPU USB Dual VGA KVM Console Extender over CAT5 UTP lets you Operate a Dual VGA PC or KVM switch up to 650ft (200 m) away, as if it was installed locally, at high-definition 1920x1200 resolution. PC connection cables are included with this product for a ready to use solution.

The dual VGA cat5 KVM extender supports easy to use hot-key and push button commands which allow you to switch between local and remote connected systems, while console connections at both ends of your setup provide easy access to all connected systems from either location. The hot-key commands also provide video adjustment controls for optimizing picture quality over varying distances. Extending over two standard Cat 5 (or better) cables gives you the ability to use existing infrastructure wiring to achieve remote access to your server or KVM switch.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for controlling a PC in an area where fan or hard drive noise is unacceptable such as a television broadcast studio

- Control/Monitor a remote server from a harsh environment where the PC would not function properly due to heat/dust/etc. (factory, warehouse, mining, etc.)
- Can act as a thin client for power users controlling powerful rack mounted servers as their desktop machines
- Use one or more servers in a server room from a remote location within the same building or campus

Features

- Dual VGA KVM extender at 1920x1200 resolution
- Can be used with a single computer or connected to an existing KVM switch
- Extend up to 650 ft. (200 m) using 2 industry-standard UTP network cables
- KVM console connections available on both the local and remote end
- Supports most combo keyboard and mouse sets (including Wireless)
- Intuitive hot-key commands for fine-tuning video

Hardware

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	Yes

Performance

IP Control	No
Max Transfer Distance	200m [656ft]
Maximum Analog Resolutions	1920x1200
Supported Resolutions	1920x1200 @ 650 ft (200m)

MTBF	65000 hours
<hr/>	
Connector(s)	
Console Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)
	2 - VGA (15 pin, High Density D-Sub)
Host Connectors	2 - VGA (15 pin, High Density D-Sub)
Other Interface(s)	2 - RJ-45
<hr/>	
Software	
OS Compatibility	OS independent; No software or drivers required
<hr/>	
Special Notes / Requirements	
Note	Product weights/measurements and connector types indicate a single unit only (either Host or Remote)
<hr/>	
Power	
Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2A
Output Voltage	12V DC
Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4
<hr/>	
Environmental	
Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0~80% RH
<hr/>	
Physical Characteristics	
Color	Black

Material	Steel
Product Length	6.1 in [15.5 cm]
Product Width	3.1 in [8 cm]
Product Height	1.6 in [4 cm]
Weight of Product	18.9 oz [535 g]

Packaging Information

Package Quantity	1
Package Length	14.4 in [36.6 cm]
Package Width	9.3 in [23.7 cm]
Package Height	3.0 in [7.7 cm]
Shipping (Package) Weight	4.7 lb [2.1 kg]

What's in the Box

Included in Package	1 - Local Unit
	1 - Remote Unit
	2 - 6ft 2-in-1 USB VGA KVM Cables
	2 - 4ft VGA Cables
	1 - Universal Power Adapter (NA/EU/UK/AU)
	8 - Rubber Feet
	1 - Instruction Manual

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*