

## 10 ft 2-in-1 Universal USB KVM Cable

**Product ID:** SVUSB2N1\_10



The SVUSB2N1\_10 10ft (3m) 2-in-1 USB + VGA KVM switch Cable is constructed of high quality materials and is expertly designed to ensure crystal clear display quality, and reliable connections.

Our universal USB KVM switch cables prevent tangles and keep your workspace neat, while delivering excellent performance with your StarTech.com or other KVM switch.

Works with:

Compatible StarTech.com KVMs can be found under the Accessories section.

Aten models (CS102U, CS104U)

Belkin models (F1DN102U, F1DN104U, F1DN108U)

TrippLite models (B006-004-R)

Cables to go models (35555, 35566, 35554, 52064)

IOGear models (GCS102U, GCS104U)

## Certifications, Reports and Compatibility



## Applications

- Connect PCs or servers to your StarTech.com or other KVM switch

## Features

- Coaxial video cable for a crystal clear display
- Bonded design reduces tangles

---

### Connector(s)

	Warranty	Lifetime
Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)	
	1 - VGA (15 pin, High Density D-Sub)	
Connector B	1 - USB B (4 pin)	
	1 - VGA (15 pin, High Density D-Sub)	

---

### Physical Characteristics

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	15.5 oz [440.0 g]

---

### Packaging Information

Package Quantity	1
Package Length	13.5 in [34.3 cm]
Package Width	5.4 in [13.6 cm]
Package Height	1.4 in [3.5 cm]
Shipping (Package) Weight	15.5 oz [438.0 g]

---

### What's in the Box

Included in Package

1 - 10 Ft. USB+VGA 2-in-1 KVM Switch Cable

---

**Warranty  
Information**

---

Warranty

Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***

