

Dual-Monitor Thunderbolt Mini Dock, 4K 60Hz DisplayPort, Driverless Hub for Windows & Mac, Gigabit Ethernet, 1x USB-A (USB 5Gbps), 11in (28cm) Cable

**Product ID:** TB3DKM2DPL



This certified Thunderbolt 3 docking station is a compact mini dock, delivering essential connections for productivity. The bus-powered dock connects dual 4K DisplayPort displays, Gigabit Ethernet, and one USB-A port and for flexible set up, the attached Thunderbolt cable has an extended length of (11 in./ 28 cm).

Great for editing 4K video or other Ultra HD tasks, this portable Thunderbolt to DisplayPort dock supports 40 Gbps of throughput and 4K resolution at 60Hz on dual DisplayPort monitors, through a single Thunderbolt port. Run resource-demanding applications on two independent displays without draining system resources.

Connect your laptop to:

- 2x 4K DisplayPort (DP) displays (up to 4096 x 2160p @ 60Hz)

At just 2.4" x 4.9" (6.1 cm x 12.4 cm), this dock takes up minimal room on your desk and in your laptop case. The dock's 28 cm (11 inches) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands, or if needed, offers the flexibility to position dock further away from the laptop on your desk.

- 1x USB 5Gbps Type-A port
- 1x Gigabit Ethernet port (with PXE Boot and Wake-on-LAN support)

As many high powered, later generation laptops optimally require more than 100W of power to stay charged, some users prefer to use their laptop's power adapter vs. using their docking stations to keep laptops charged.

This bus-powered TB mini dock is ideally suited for those users, providing full Thunderbolt docking station performance and functionality, while their workstation laptops are separately charged."

## Certifications, Reports and Compatibility



## Applications

### Features

- **HIGH-PERFORMANCE THUNDERBOLT 3 CERTIFIED DOCK:** Driverless setup for plug-and-play installation; Thunderbolt (40 Gbps); Dual 4K 60Hz DisplayPort (DP) outputs; 1x USB 5Gbps port; Gigabit Ethernet port with PXE boot and WoL
- **FOR HIGH-POWERED LAPTOPS:** Dual 4K 60Hz video output with direct GPU performance and no software or compression; Ideal for high-performance laptops that need a direct power adapter connection, but require Thunderbolt 3 dock performance & functionality
- **COMPATIBILITY:** This docking station is compatible with Windows, macOS, and Ubuntu; Supports Thunderbolt or USB4 laptops; Dual Display on M1, M2, M3 Max/Pro, M4 Pro/Max MacBooks, and single display on base M-series MacBooks and iPad Pro M1 & later
- **EXTRA-LONG CABLE:** Attached 11in (28cm) cable provides long reach for easy setup and prevents adapter from dangling on the host connector; Ideal cable length to reduce port strain on 2-in-1 convertible laptops, or host laptops on riser stands
- **THE IT PRO'S CHOICE:** Our docking stations are rigorously tested in our Innovation Lab to ensure enterprise-grade reliability and cross-platform compatibility; Built to support large-scale deployments, Windows 11 upgrades, and the shift to AI-enabled PCs

---

### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	2
Audio	No

Interface	Thunderbolt 3
Bus Type	Thunderbolt 3
Industry Standards	1Gb connectivity to any 1000Base-T device (IEEE802.3ab Compliant) 100Mb connectivity to any 100Base-TX device (IEEE802.3u Compliant) 10Mb connectivity to any 10Base-T device (IEEE802.3i Compliant)
Chipset ID	Intel JHL6540 (Alpine Ridge) Texas Instruments TPS65983A Parade PS176 ASMedia ASM1042A Intel WGI210

---

**Performance**

Wake On Lan	Yes
Maximum Digital Resolutions	4K 60Hz
Compatible Networks	10/100/1000 Mbps
PXE	Yes

---

**Connector(s)**

External Ports	2 - DisplayPort (20 pin) 1 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps) 1 - RJ-45
Host Connectors	1 - Thunderbolt 3 USB-C (24-pin) (40Gbps)

---

**Software**

OS Compatibility	Windows 11, 10 (32/64 bit), 8.1 (32/64bit), 7 (32/64bit), Windows Server 2008 R2, 2012(32/64bit), macOS 10.10 -10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1
------------------	--

---

**Special Notes / Requirements**

Note	MacBook Air and MacBook Pro systems using the new Apple M1
------	--

chip support only a single external display over the Thunderbolt 3 ports, even when connected to a Thunderbolt 3 docking station with more than one video output. This single monitor limitation does not affect Intel-based Macs with Thunderbolt 3.

---

**Power**

Power Source	Bus Powered
--------------	-------------

---

**Environmental**

Operating Temperature	5C to 40C
Storage Temperature	-20C to 70C
Humidity	0% to 95% (non-condensing) at 25C

---

**Physical Characteristics**

Color	Black & Silver
Material	Aluminum and Plastic
Cable Length	11.0 in [28 cm]
Product Length	4.9 in [12.4 cm]
Product Width	2.7 in [6.9 cm]
Product Height	1.1 in [2.7 cm]
Weight of Product	5.2 oz [147.8 g]

---

**Packaging Information**

Package Length	8.3 in [21.0 cm]
Package Width	5.8 in [14.7 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	9.4 oz [266.0 g]

---

**What's in the Box**

Included in Package	1 - Docking Station
	1 - User Manual

---

**Warranty Information**

Warranty

3 Years

---

*\*Product appearance and specifications are subject to change without notice.*

