

2.6ft (80cm) Thunderbolt 3 Cable, 40Gbps, 100W PD, 4K/5K, Thunderbolt Certified, Compatible with Thunderbolt 4/USB 3.2/DisplayPort

Product ID: TBLT34MM80CM



This Thunderbolt 3 to Thunderbolt 3 cable lets you deliver video, data and power to your Thunderbolt 3, USB 3.2 and DisplayPort devices. At 0.8 meters in length, the Thunderbolt cable provides added flexibility and distance when connected to your devices.

Fully compatible with your USB 3.2 Gen 2 devices, this cable can be used for charging and syncing your mobile devices. Also, connect and power USB-C laptops, such as your MacBook or Chromebook, and USB-C peripherals, such as your docking station.

This Thunderbolt 3 USB-C cable supports data transfer rates up to 40Gbps when connected to a Thunderbolt 3 device, enabling lightning fast performance. When connected to a USB 3.2 device, this cable supports rates of 20Gbps.

This cable supports dual 4K 60Hz or full 5K 60Hz video for an astonishing resolution, contrast, and color depth.

The Thunderbolt 3 Type-C cable delivers up to 100W of power for charging a Thunderbolt 3 laptop, which means you can keep your devices powered without using an additional power supply.

Bridge multiple Thunderbolt 3 USB-C enabled laptops for peer-to-peer 10GbE networking with this cable. It's also perfect for sharing peripherals such as printers and storage.

TBLT34MM80CM is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your Thunderbolt 3 devices
- Power and charge Thunderbolt 3 devices
- Charge USB 3.2 mobile devices
- Peer-to-peer networking for various Thunderbolt 3 laptops

Features

- **HIGH PERFORMANCE:** 80cm (2.6ft) Passive Thunderbolt 3 cable delivers consistent 40 Gbps and 100W charging; Connect a Thunderbolt 4 / 3 / USB-C laptop, or iPad Pro (5th gen and later) to a docking station or UHD monitor
- **THUNDERBOLT CERTIFIED:** Intel Thunderbolt-certified for guaranteed compatibility with Thunderbolt hosts and devices; Supports up to 5K 60Hz or dual 4K 60Hz
- **QUALITY CONSTRUCTION:** Coaxial wire with braided alloy shield for enhanced EMI protection; Robust strain reliefs on connectors for improved durability
- **APPLICATIONS:** Facilitate a Thunderbolt 3 or USB-C connection supporting full 40 Gbps, video, and power; Ideal for reliable performance in high-bandwidth applications such as external PCIe chassis/storage drives, and Thunderbolt networking devices
- **SPECS:** 2.6ft (80cm); Thunderbolt 3 (40 Gbps); 5K 60Hz; 100W PD 3.0; Cable Outer Diameter: 0.19in (4.7mm); Color: Black

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	Thunderbolt 3 - 40 Gbit/s
---------------	---------------------------

Connector(s)

Connector A	1 - Thunderbolt 3 USB-C (24-pin) (40Gbps)
Connector B	1 - Thunderbolt 3 USB-C (24-pin) (40Gbps)

Physical Characteristics

Color	Black
Cable Length	2.6 ft [0.8 m]
Product Length	31.5 in [80.1 cm]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [0.6 cm]
Weight of Product	1.2 oz [35.0 g]

Packaging Information

Package Quantity	1
Package Length	5.0 in [12.7 cm]
Package Width	8.6 in [21.9 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	1.6 oz [44.0 g]

What's in the Box

Included in Package	1 - 0.8 m Thunderbolt 3 Cable
---------------------	-------------------------------

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

