

2U Sliding Server Rack Mount Shelf - 20 to 30in Adjustable Mounting Depth - Vented - 50lb - Heavy Duty Universal 19" Rack Shelf for Equipment Rack - 24in Deep

Product ID: UNISLDSHF19



The UNISLDSHF19 19in Vented Adjustable Mounting Depth Sliding Server Rack Cabinet Shelf offers a simple way to install non rack mountable equipment into a server cabinet or open server rack.

Offering a weight capacity of up to 50 lbs (22.7 kg), the sliding rack shelf features a ventilated, cold-rolled steel shelf on two locking adjustable rails which allow the shelf to be installed into cabinets or racks with mounting depths from 20in (510mm) to 30in (744mm). The locking feature locks the shelf 3/4 of the way out, preventing the shelf from accidentally falling out of the rack or sliding back in before maintenance is complete.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Add a sliding rack mounting option for non rack mountable equipment

Features

- UNIVERSAL 19" FIT: Add a sliding shelf to a server rack or cabinet for easy peripheral and equipment access; This 19in rack mount tray has a locking feature, preventing the shelf from falling out

- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with cold rolled steel, the sturdy IT-grade pull out server rack shelf ensures long term durability and supports a total weight load of 50lb (22.7kg)
- **COMPACT DESIGN:** The 2U server rack shelf features a compact form factor, making it ideal for rackmount equipment, tools and peripherals in your home, studio or office space
- **VERSATILE FUNCTIONALITY:** This 24in (60cm) deep sliding cabinet shelf is ideal for adding additional sliding storage space for your IT or AV accessories; It is also vented to ensure consistent airflow
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Industry Standards	EIA RS310-C

Performance

Weight Capacity (Stationary)	50.0 lb [22.7 kg]
---------------------------------	-------------------

Physical Characteristics

Color	Black
Material	Steel
Product Length	24.0 in [60.9 cm]
Product Width	19.0 in [48.2 cm]
Product Height	3.5 in [8.8 cm]
Weight of Product	15.4 lb [7.0 kg]
Maximum Mounting Depth	29.3 in [74.4 cm]
Minimum Mounting Depth	20.1 in [51.0 cm]

Packaging Information

Package Quantity	1
------------------	---

Package Length	21.6 in [54.8 cm]
Package Width	27.6 in [70.1 cm]
Package Height	6.9 in [17.6 cm]
Shipping (Package) Weight	18.4 lb [8.3 kg]

What's in the Box

Included in Package	1 - Sliding Shelf
	8 - M6 Screws
	8 - M6 Cage Nuts
	1 - Quick-Start Guide

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***