

4-Port USB 2.0-Over-Cat5-or-Cat6 Extender - 130ft (40m) - TAA

Product ID: USB2004EXTV



This 4-port USB 2.0 extender is an easy and inexpensive solution for creating workspace freedom. Now you can extend the distance of your USB 2.0 devices over a single Ethernet cable, up to 130ft (40m) over Cat5 or Cat6.

Overcome the 16ft USB cable length limitation to create a more flexible and efficient workspace. Now you can place up to four USB devices in remote locations away from the host computer system. Position your hard drive enclosure, printer, scanner, webcam and other popular peripherals right where you need them, to save time and enhance your productivity.

Gain quick access to the USB devices you use most frequently. Often on the go? Use the two top ports for fast, easy connections to portable devices like flash drives, smartphones and tablets. Plus, you still have two front-facing ports for printers or other devices requiring a more permanent set-up.

The versatile USB2004EXTV supports Windows, Mac and Linux systems. Set-up is easy with no additional drivers or software required, and the extender is backward compatible with USB 1.1 and 1.0 peripherals.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- No need to lay new wiring – use existing direct cable, in-wall Cat5 or Cat6, to extend USB connections between rooms
- Use as a mid-point repeater to increase the connection distance of your USB peripherals

Features

- Place your devices where you need them with this cost-effective USB extender
- Unique 4-port design with 2 ports on top for easy access
- OS independent for fast, hassle-free set-up
- Kit includes a transmitter and a 4-port hub receiver
- Supports transfer rates of up to 480 Mbps
- Plug-and-play and hot-swap compatible

Hardware

Warranty	2 Years
Ports	4
Cabling	Cat 5 UTP or better

Performance

Maximum Data Transfer Rate	480Mbps
Max Distance	40m [131ft]

Connector(s)

Local Unit Connectors	1 - USB Mini-B (5 pin)
	1 - RJ-45
Remote Unit Connectors	4 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - RJ-45

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes /

Requirements

System and Cable Requirements	USB-enabled computer system with an available USB port
	RJ45 terminated Cat5 or higher Ethernet cabling

Indicators

LED Indicators	1 - Power / Link
----------------	------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4 A
Output Voltage	5 DC
Output Current	2.0 A
Center Tip Polarity	Positive
Plug Type	N
	N
Power Consumption (In Watts)	10

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~80% RH

Physical Characteristics

Color	Black
Material	Steel
Product Length	3.1 in [8.0 cm]
Product Width	2.0 in [5.2 cm]
Product Height	0.9 in [2.2 cm]
Weight of Product	11.3 oz [319.0 g]

Packaging Information

Package Quantity	1
Package Length	9.2 in [23.4 cm]
Package Width	6.1 in [15.6 cm]
Package Height	2.7 in [6.8 cm]
Shipping (Package) Weight	1.6 lb [0.7 kg]

What's in the Box

Included in Package	1 - USB 2.0 Local Extender
	1 - USB 2.0 Remote Extender
	1 - 0.5m (1.5ft) Mini-USB to USB 2.0 A Cable
	1 - 1.5m (5ft) RJ45 Ethernet Cable
	8 - Rubber Feet
	1 - Universal Power Adapter (NA/JP, EU, UK, ANZ)
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*