

25m USB 2.0 Active Extension Cable - M/F - TAA

Product ID: USB2AAEXT25M



The USB2AAEXT25M 25m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 25-meters (80-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Plus you can daisy chain 2 cables for a total USB extension of up to 50-meters.

If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT25M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain 2 cables together for even longer USB extensions

Features

- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- Compatible with PC Windows 8/7/Vista/XP and Mac computer systems

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

Special Notes / Requirements

Note	Cascade two USB2AAEXT25M devices together for further extension
------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	5

Environmental

Operating Temperature	0C to 70C (32F to 122F)
Storage Temperature	-20C to 85C (-4F to 185F)

Physical Characteristics

Color	Black
Connector Style	Straight
Cable Length	82.0 ft [25 m]
Product Length	3.4 in [86.5 mm]
Product Width	0.9 in [22 mm]
Product Height	0.5 in [12 mm]
Weight of Product	2.3 lb [1.0 kg]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.7 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.4 in [6.1 cm]
Shipping (Package) Weight	2.8 lb [1.3 kg]

What's in the Box

Included in Package	1 - 25m USB 2.0 Active Extension Cable - M/F
	1 - Universal Power Adapter
	1 - Plug Adapters for North America, UK, Europe, and Australia

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***