

## 5m USB 2.0 Active Extension Cable - M/F - TAA

Product ID: USB2AAEXT5M



The USB2AAEXT5M 5m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 5-meters (15-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables. Plus you can daisy chain 4 cables for a total USB extension of up to 20-meters.

If necessary, the cable can be powered from a wall outlet using the Universal AC power adapter that was provided with the cable – this will allow you to use USB bus-powered devices that may require extra power.

The USB2AAEXT5M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain up to 4 cables together for even longer USB extensions

### Features

- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring

---

**Hardware**

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

---

**Special Notes / Requirements**

Note	Cascade up to 4 USB2AAEXT5M cables together for further extension
------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	5

---

**Physical**

#### Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	16.4 ft [5 m]
Product Length	3.4 in [86.5 mm]
Product Width	0.9 in [22 mm]
Product Height	0.5 in [12 mm]
Weight of Product	8.0 oz [227 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	8.4 in [21.4 cm]
Package Height	2.4 in [6.2 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

---

#### What's in the Box

Included in Package	1 - 5m USB 2.0 Active Extension Cable - M/F
	1 - Universal Power Adapter
	1 - Plug Adapters for North America, UK, Europe, and Australia

---

#### Warranty Information

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*