

1ft (30cm) USB-A to USB-C Charging Cable, Charge & Sync, 3A, USB 2.0, TPE Jacket - Black USB Charging Cord

**Product ID:** USB2AC1FTBK



Charge a USB Type-C mobile device or transfer files to a USB-A host computer with this high-quality USB-A to Type-C cable. The USB-A to USB-C charger cord supports up to 15W and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent or daily use, the USB-A to USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

The 1-foot (0.3-meter) USB Charging Cable is the ideal length for charging mobile devices on the go, or minimizing cable clutter on compact desk setups.

Facilitating up to 3A of output, the USB-C Charger Cord can fast-charge a smartphone or tablet. To use, connect the cable from a USB-C device to a USB-A wall charger or host device

## Certifications, Reports and Compatibility



## Applications

## Features

- **USB-A TO USB-C CHARGING:** High quality USB-A to Type-C cable delivers 3A output for fast charging portable

USB-C devices; Connect this cable to a USB-A wall charger, power bank, or charge/access your phone/tablet from a USB-A host

- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 12.7mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for fast charging phones and other small peripherals; Supports USB 2.0 (480Mbps) for general use, including file transfer and device synchronization when connected to a USB-A host computer or external storage
- **PERFORMANCE:** Supports 15W/3A Fast Charge; USB 2.0 (480Mbps); Length: 1-foot (0.3-meter); Color: Black; O.D.: 0.11in (3mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **COMPATIBILITY:** Compatible with a wide range of USB-C devices when connected via a USB-A port, including iPhone 16 Plus/Pro/Max and up, Samsung Galaxy S8 and up, Google Pixel and other smartphones/tablets; Not recommended for charging USB-C laptops/displays

---

#### Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Performance

MTBF	Rated for 10,000+ insertion cycles
------	------------------------------------

---

#### Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-C

---

#### Special Notes / Requirements

Note	Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)
------	--

---

#### Power

Power Delivery	15W
Input Current	3A

---

#### Environmental

---

Operating Temperature	-10 to 60 (14&degF to 140&degF)
Storage Temperature	-20 to 70 (-4&degF to 158&degF)
Humidity	5%~85%

---

#### **Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24/32 AWG
Material	Polyamide Resin
Cable Length	1.0 ft [0.3 m]
Cable OD	0.1 in [3 mm]
Product Length	12.4 in [315 mm]
Product Width	0.6 in [15.8 mm]
Product Height	0.3 in [7.6 mm]
Weight of Product	0.4 oz [12 g]

---

#### **Packaging Information**

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.2 in [5.0 mm]
Shipping (Package) Weight	0.6 oz [17.0 g]

---

#### **What's in the Box**

Included in Package	1 - USB-A to USB-C Cable
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***