

4m (13ft) USB-A to USB-C Charging Cable, Charge & Sync, 3A, USB 2.0, TPE Jacket - Black USB Charging Cord

Product ID: USB2AC4MBKE



Charge a USB Type-C mobile device or transfer files to a USB-A host computer with this high-quality USB-A to Type-C cable. The USB-A to USB-C charger cord supports up to 15W and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent or daily use, the USB-A to USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

The 4m (13ft) USB Charging Cable is the ideal length for larger desk workstations or for use in locations where extra length is desired.

Facilitating up to 3A of output, the USB-C Charger Cord can fast-charge a smartphone or tablet. To use, connect the cable from a USB-C device to a USB-A wall charger.

Certifications, Reports and Compatibility



Applications

Features

- **USB-A TO USB-C CHARGING:** High quality USB-A to Type-C cable delivers 3A output for fast charging portable

USB-C devices; Connect this cable to a USB-A wall charger, power bank, or charge/access your phone/tablet from a USB-A host

- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for fast charging phones and other small peripherals; Supports USB 2.0 (480Mbps) for general use, including file transfer and device synchronization when connected to a USB-A host computer or external storage
- **PERFORMANCE:** Supports 15W/3A Fast Charge; USB 2.0 (480Mbps); Length: 4-meter (13.1-foot); Color: Black; O.D.: 0.17in (4.2mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **COMPATIBILITY:** Compatible with a wide range of USB-C devices including iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Google Pixel, USB-C portable monitors Asus ZenScreen/ProArt, iPad Pro, MacBook Air/Pro, Surface Book, and more

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

MTBF	Rated over 10,000 insertion cycles
------	------------------------------------

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-C

Special Notes / Requirements

Note	Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)
------	--

Power

Power Delivery	15W
Input Current	3A

Environmental

Operating Temperature	-10 to 60 (14°F to 140°F)
Storage Temperature	-20 to 70 (-4°F to 158°F)
Humidity	5%~85%

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	22/26 AWG
Material	Polyamide Resin
Cable Length	13.1 ft [4 m]
Cable OD	0.2 in [4.2 mm]
Product Length	13.2 ft [4.0 m]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [7.8 mm]
Weight of Product	4.8 oz [136 g]

Packaging Information

Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.6 in [1.5 cm]
Shipping (Package) Weight	5.6 oz [158.0 g]

What's in the Box

Included in Package	1 - USB-A to USB-C Cable - M/M
---------------------	--------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*