

USB 3.0 (5Gbps) Cable - A to A - M/M - 3 m (10 ft.)

**Product ID:** USB3SAA3MBK



This USB 3.2 Gen 1 (5Gbps) cable, also known as a USB 3.0 cable, lets you connect your USB-A devices as needed throughout your workspace. With a connection distance of up to 3 meters (10 feet), you can organize your PC and USB hub, or other USB-A devices, to match your configuration needs.

Plus, this high-quality cable features Shielded Twisted Pair (STP) construction, which helps to prevent electro-magnetic interference and ensure reliable data communication.

The USB3SAA3MBK is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Connect your USB 3.0 USB-A devices, such as a USB hub, to a desktop or server

## Features

- Position your USB 3.2 Gen1 devices as needed throughout your workspace
- Molded connectors with strain relief
- Guaranteed reliability

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Performance**

Type and Rate	USB 3.0 - 5 Gbit/s
Insertion Rating	5000 Cycles

---

**Connector(s)**

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

---

**Environmental**

Operating Temperature	-20C to 85C (-4F to 185F)
Storage Temperature	-20C to 85C (-4F to 185F)
Humidity	65%

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.6 in [1.5 cm]
Product Height	0.3 in [0.8 cm]
Weight of Product	4.0 oz [112.0 g]

---

**Packaging Information**

Package Quantity	1
------------------	---

Package Length	6.5 in [16.6 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.9 in [2.4 cm]
Shipping (Package) Weight	4.5 oz [128.0 g]

---

#### What's in the Box

Included in Package	1 - 3m USB 3.0 A to A Cable - M/M - Black
---------------------	---

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***

