

Dual Monitor USB 3.0 Laptop Docking Station with HDMI & DVI/VGA, 6x USB-A Hub, GbE, Audio, Universal Type-A Dock - Windows/macOS/ChromeOS - TAA

**Product ID:** USB3SDOCKHD



This USB 3.0 dock combines a 6 port USB 2.0/USB 3.0 hub, headphone and microphone audio connectors, and a Gigabit Ethernet RJ45 port into a single docking station.

Offering flexible dual video combinations right out-of-the-box, this universal laptop docking station features HDMI and DVI external monitor output providing up to 1920x1200p resolutions, as well as an included DVI to VGA adapter for added flexibility.

The built-in USB hub features 2 USB 3.0 ports and 4 USB 2.0 ports for connecting extra peripherals such as external hard drives or a wired mouse as if they connected directly to your laptop.

With an upright design, the dock occupies as little desk space as your smart phone, so it's perfect for hoteling or hot desk environments.

The integrated RJ45 Ethernet port supports speeds of 10/100/1000 Mbps, giving you an instant connection to a reliable wired network.

StarTech.com's laptop docking stations can be used for cost savings and faster deployment with just a single cable. This USB 3.0 Docking Station is backed by a competitive 3-year warranty and free lifetime multilingual Technical Support.

## Certifications, Reports and Compatibility





## Applications

- Shared workspaces
- Hot/Remote desks
- Convert laptop to desktop workstation

## Features

- **UNIVERSAL DOCKING STATION:** USB 3.0 docking station dual monitor features built-in 1x HDMI and 1x DVI monitor outputs; DVI to VGA adapter included for compatibility with VGA monitors; 1920 x 1200p maximum resolution on two displays
- **INCREASED PRODUCTIVITY:** This dual monitor universal docking station for laptops combines 4x USB 2.0 ports, 2x USB 3.2 Gen 1 (5Gbps) hub ports, headphone & microphone audio jack, and a Gigabit Ethernet RJ45 port into a single IT-grade dock
- **UPRIGHT DESIGN:** The high performance, all black, upright dock features a slim & sleek design that is the perfect addition to any home or office workstation; The dock enhances your laptop's capabilities while taking up little desk space
- **UNIVERSAL COMPATIBILITY:** Compatible with Windows, macOS, & Chrome OS v55+, enabling extended dual displays on Laptops, Ultrabooks, Chromebooks and MacBooks that feature a USB-A host connection; Supports HDMI, DVI and VGA monitors
- **CONNECTIVITY TOOLS:** Optimize the performance and security of this USB 3.0 docking station, using the included MAC Address Changer, USB Event Monitoring, Windows Layout & Wi-Fi Auto Switch utilities (available for download)

---

### Hardware

Warranty	3 Years
4K Support	No
Fast-Charge Port(s)	No
Displays Supported	2
Bus Type	USB 3.2 Gen 1 (5Gbps)

Industry Standards	IEEE 802.3, 802.3u, and 802.3ab
Chipset ID	DisplayLink - DL-3900
	VIA/VLI - VL810
	Terminus - FE1.1
	Realtek - RTL8211E

---

### Performance

Maximum Digital Resolutions	1920 x 1200 Lower resolutions are also supported.
Type and Rate	USB 3.0 - 5 Gbit/s USB 2.0 - 480 Mbit/s
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

---

### Connector(s)

Connector Type(s)	2 - 3.5 mm Mini-Jack (3 Position) 1 - DVI-I (29 pin) 1 - HDMI (19 pin) 1 - RJ-45 2 - USB Type-A (9 pin, 5 Gbps) 1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps) 4 - USB 2.0 Type-A (4 pin, 480Mbps)
-------------------	--

---

### Software

OS Compatibility	Windows XP SP3 (32-bit), Vista, 7, 8, 8.1, 10, 11 macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1 Chrome OS v55+Ubuntu 18.04, 20.04, 22.04, 24.04, 24.04 
------------------	--

---

### Special Notes / Requirements

---

System and Cable Requirements	CPU: i3 Dual core 2.8GHz or better, RAM: 2GB or higher, Available USB 3.0 port
Note	The DVI-I connector supports DVI-I signaling (digital and analog)

---

**Indicators**

LED Indicators	1 - Power (Blue) 1 - USB Hub Link (Blue)
----------------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A
Output Voltage	5 DC
Output Current	4A
Plug Type	C
Power Consumption (In Watts)	20

---

**Environmental**

Operating Temperature	10C to 40C (50F to 104F)
Storage Temperature	-10C to 80C (14F to 176F)

---

**Physical Characteristics**

Color	Black
Material	Plastic
Product Length	4.9 in [12.5 cm]
Product Width	2.8 in [7.0 cm]
Product Height	7.7 in [19.5 cm]
Weight of Product	13.1 oz [370.0 g]

---

**Packaging Information**

Package Quantity	1
------------------	---

Package Length	7.5 in [19.1 cm]
Package Width	11.1 in [28.3 cm]
Package Height	4.3 in [10.9 cm]
Shipping (Package) Weight	2.0 lb [0.9 kg]

---

#### What's in the Box

Included in Package	1 - USB 3.0 Docking Station 1 - 3.3 ft [1 m] USB 3.0 Cable 1 - DVI to VGA Adapter 1 - Universal Power Adapter (NA/JP, EU, UK, ANZ) 1 - Instruction Manual
---------------------	---

---

#### Warranty Information

Warranty	3 Years
----------	---------

---

***\*Product appearance and specifications are subject to change without notice.***

