

USB 3.0 Mini Dock - Dual Monitor USB-A Docking Station with DisplayPort 4K 60Hz Video & Gigabit Ethernet - 1ft (30cm) cable - Portable USB 3.1 Gen 1 Type-A Laptop Adapter - TAA

**Product ID:** USBA2DPGB



This USB to Dual DisplayPort Mini Dock provides your USB 3.0 laptop with connectivity for dual 4K 60 Hz monitors and Gigabit LAN - enabling you to quickly harness dual-display productivity and network connectivity.

The dual DisplayPort adapter adds two DP video outputs to your USB laptop, with resolution support up to 4K. Working on two monitors increases your productivity by giving you more screen space. You can simultaneously access multiple applications and reference material on one display while composing on the other.

Ethernet ports on modern laptops are uncommon, and wireless networks are less secure and less reliable than a hardwired connection. With the GbE port on this portable docking station that features an Ethernet adapter you can access wired LANs even if your USB 3.0 laptop doesn't have an Ethernet port.

The dock features a compact design that's perfect for business professionals who need portable office desk accessories for traveling between multiple office locations, or shared workspaces.

The USBA2DPGB is TAA compliant and backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility





## Applications

- Keep your docking station with your laptop while traveling
- Perform high-resolution tasks like graphic design or video editing on two 4K 60Hz monitors
- Connect to hardwired networks in offices that avoid wireless networks

## Features

- **USB-A DUAL 4K 60HZ MINI DOCK:** USB 3.0 mini dock with dual monitor DisplayPort, GbE port; DisplayLink certified, DL 6950 chipset supports dual DP 4K 60Hz video output & widespread display compatibility
- **EASY INSTALLATION:** Portable USB Type-A docking station with a 1ft (30cm) attached cable to provide setup flexibility & extended port reach to devices like USB-A Surface Pros to reduce port strain
- **DESIGNED FOR PORTABILITY:** This bus-powered USB-A mini docking station has a compact form factor and it is ideally suited for small in-office or work-from-home workspaces
- **WIDE DEVICE COMPATIBILITY:** This mini dock is compatible with wide range of USB-A laptops, ultrabooks, chromebooks and Surface Pros
- **EASY TO SETUP AND DEPLOY:** This USB-A (USB 3.0/USB 3.1 Gen 1) multiport adapter hub features automatic driver setup and supports multiple OS platforms including Windows & Chrome OS

---

### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	2
Bus Type	USB 3.2 Gen 1 (5Gbps)
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
	USB 3.0 - Backward compatible with USB 2.0/1.1
Chipset ID	DisplayLink - DL-6950

---

### Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	Single display - DisplayPort - 5120 x 2880 @ 60Hz (using two DP ports)  Dual displays - DisplayPort - 4096 x 2160 @ 60Hz / 3840 x 2160 @ 60Hz
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	No
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

---

**Connector(s)**

Connector Type(s)	2 - DisplayPort (20 pin)  1 - RJ-45  1 - USB Type-A (9 pin, 5 Gbps)
-------------------	---

---

**Software**

OS Compatibility	Windows XP (32-bit), Vista, 7, 8, 8.1, 10, 11, macOS 10.6 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1, Ubuntu 18.04, 20.04, 22.04, 24.04  Linux Kernel 4.2 and up - LTS Versions only, Chrome OS v55+,
------------------	---

---

**Special Notes / Requirements**

System and Cable Requirements	A host laptop with an available USB-A port.
Note	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.  4K resolution is supported on both video ports. A 4K-capable DisplayPort display is required to achieve 4Kx2K resolution.

---

**Power**

Power Source	USB-Powered
Output Voltage	5 DC

---

**Environmental**

---

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	10-90% RH

---

**Physical Characteristics**

Color	Black
Cable Length	11.8 in [300 mm]
Product Length	5.1 in [13 cm]
Product Width	2.3 in [5.8 cm]
Product Height	0.8 in [2 cm]
Weight of Product	4.4 oz [126 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.0 in [20.4 cm]
Package Width	4.6 in [11.6 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	8.1 oz [230.0 g]

**What's in the Box**

Included in Package	1 - mini dock
	1 - quick-start guide

**Warranty Information**

Warranty	3 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*