

DVI to USB-C Video Capture Device - 1080p 60fps - TAA

Product ID: USBC2DVCAPRO



This DVI to USB-C video capture device works as an external USB capture card to record high-definition DVI video to your USB-C, USB-A or Thunderbolt 3 computer. With an aluminum enclosure, this device is built strong for fixed-location or on-the-go capture. It offers a separate 3.5 mm audio input for accompanying audio or voice-overs, and a DVI pass-through port for connecting a monitor to review the video as it's captured.

Ensures smooth integration with popular streaming and recording software through DirectShow support. Instantly stream your video source over the Internet using online services such as Twitch.

With this DVI to USB video capture device, you can record meetings, presentations, conference calls and security footage, saving 1080p HD video at 60fps directly to your computer for easy editing and sharing.

With this DVI to USB 3.0 video capture device, you can record raw/lossless video using any third-party DirectShow compatible software, such as Open Broadcaster Software (OBS).

Certifications, Reports and Compatibility



Applications

- Record video for training and tutorial purposes

- Capture live video by connecting the camera directly to the device
- Live stream the connected video source over the internet

Features

- **CROSS-PLATFORM COMPATIBILITY:** Supports both Windows and macOS with UVC drivers and DirectShow support for integration with professional video capture and streaming software
- **1080P 60FPS USB VIDEO CAPTURE:** Captures Full HD video at 60 frames per second using USB 3.0 bandwidth; Delivers smooth, detailed recordings from DVI video sources
- **PORTABLE AND RUGGED DESIGN:** Encased in a durable aluminum housing, this compact capture device is ideal for mobile setups and on-location video work
- **BROAD STREAMING SUPPORT:** Compatible with third-party software via DirectShow, making it easy to stream to platforms like YouTube or Twitch using Windows-based tools
- **THE IT PRO's CHOICE:** Our video capture devices are lab-tested for DirectShow compatibility, ensuring broad software support and integration in professional AV and IT environments; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	2 Years
AV Input	DVI
AV Output	USB
Audio	Yes
Industry Standards	NTSC, PAL-M, PAL-60, PA
	Video Encoding: MPEG4/H.264
	DirectShow Compatible
Chipset ID	Mstar - MST3363CNK-170

Performance

Maximum Analog Resolutions	1920 x 1080 60 FPS
Maximum Digital Resolutions	1920 x 1080 60 FPS
Supported Resolutions	1920 x 1080, 1280 x 720, 1024 x 768, 800 x 600

Wide Screen Supported	Yes
Audio Specifications	2-channel stereo audio
MTBF	504,825 Hours

Software

OS Compatibility	Windows 8, 8.1, 10, 11
	MacOS 10.11 to 10.14

Special Notes / Requirements

Note	<p>This video capture device requires a USB 3.0 port (or higher). The video capture device does not work with USB 2.0 ports (or lower).</p> <p>The capture software included for macOS does not support video streaming</p>
------	---

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-5C to 40C (23F to 105F)
Humidity	20% to 80% (non-condensing)

Physical Characteristics

Color	Black & Gray
Product Length	3.6 in [92 mm]
Product Width	2.3 in [5.8 cm]
Product Height	1.1 in [2.8 cm]
Weight of Product	3.1 oz [88 g]

Packaging Information

Package Quantity	1
Package Length	9.2 in [23.3 cm]
Package Width	6.1 in [15.6 cm]

Package Height 2.3 in [5.8 cm]

Shipping (Package) Weight 1.2 lb [0.5 kg]

What's in the Box

Included in Package	1 - USB 3.0 capture device for DVI video
	1 - 6ft [2m] USB-C to USB-B Cable
	1 - 3.3 ft [1 m] USB-A to USB-B cable
	1 - 3.3 ft [1 m] DVI cable

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

