

## 6 ft USB 2.0 Extension Cable A to A - M/F

**Product ID:** USBEXTAA\_6



The USBEXTAA\_6 6ft USB Extension Cable (A-A) features 1 USB A male connector and 1 USB A female connector, extending the connection between USB 2.0 devices by up to 6 feet - an ideal solution for better placement of peripheral devices, or adding flexibility to existing USB ports.

This high quality USB extension cable is fully rated for use with USB 1.1 and USB 2.0 devices, and is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend your USB connection to connect a USB printer or any USB peripheral device to a PC or Mac at high-performance data transfer speed

### Features

- Designed and constructed to USB 2.0 specifications
- Molded strain relief
- Supports data transfer rates up to 480 Mbps

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel

---

**Performance**

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

---

**Physical Characteristics**

Color	Beige
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.6 in [1.6 cm]
Product Height	0.3 in [0.8 cm]
Weight of Product	2.6 oz [74.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.8 in [22.3 cm]
Package Width	4.9 in [12.4 cm]
Package Height	0.3 in [7.7 mm]
Shipping (Package) Weight	2.8 oz [78.0 g]

---

**What's in the Box**

Included in Package	1 - 6 ft USB 2.0 Extension Cable A to A - M/F
---------------------	---

---

**Warranty Information**

Warranty	Lifetime
----------	----------

*\*Product appearance and specifications are subject to change without notice.*

