

10 ft Beige A to B USB 2.0 Cable - M/M

**Product ID:** USBFAB\_10



The USBFAB\_10 10ft USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

## Features

- Supports USB 2.0 data transfer rates up to 480 Mbps

**Hardware**

Warranty	Lifetime
----------	----------

Connector Plating	Nickel
-------------------	--------

---

**Performance**

Maximum Cable Length	16.4 ft [5 m]
----------------------	---------------

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
-------------	-------------------------------------

Connector B	1 - USB B (4 pin)
-------------	-------------------

---

**Physical Characteristics**

Color	Beige
-------	-------

Cable Length	10.0 ft [3.0 m]
--------------	-----------------

Product Length	10.0 ft [3.0 m]
----------------	-----------------

Weight of Product	3.3 oz [93 g]
-------------------	---------------

---

**Packaging Information**

Package Quantity	1
------------------	---

Package Length	6.5 in [16.6 cm]
----------------	------------------

Package Width	5.0 in [12.6 cm]
---------------	------------------

Package Height	0.7 in [1.8 cm]
----------------	-----------------

Shipping (Package) Weight	3.4 oz [96.0 g]
---------------------------	-----------------

---

**What's in the Box**

Included in Package	1 - 10 ft Beige A to B USB 2.0 Cable - M/M
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*