

2 Port USB A Female Low Profile Slot Plate Adapter

Product ID: USBPLATELP



The USBPLATELP 2 Port Low Profile USB Bracket converts the USB pins on a USB 2.0 motherboard header to 2 standard USB A ports.

An ideal solution for small form factor computer cases, the slot plate can be mounted on the rear panel of your low profile or thin client computer case - adding two USB female ports for simple connection to USB peripheral devices.

The USB motherboard adapter cable is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Add two USB 2.0 female ports to the back of a small form factor computer case

Features

- 2x USB 'A' female ports
- 2x IDC-5 female connectors
- Supports 4 or 5 pin motherboard connections
- Supports high-speed USB data transfer rates of up to 480 Mbps

- Offers 11.25" in cable length

Performance

Warranty	Lifetime
Type and Rate	USB 2.0 - 480 Mbit/s

Connector(s)

Connector A	2 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	2 - IDC (5 pin, Motherboard Header)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Gray
Cable Length	11.2 in [28.5 cm]
Product Length	12.6 in [32.0 cm]
Product Width	0.8 in [2.0 cm]
Product Height	3.1 in [8.0 cm]
Weight of Product	1.6 oz [44.0 g]

Packaging Information

Package Quantity	1
Package Length	7.2 in [18.2 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.8 in [2.1 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

What's in the Box

Included in Package	1 - 2 Port USB A Female Low Profile Slot Plate Adapter
---------------------	--

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

