

3 ft Panel Mount USB Cable B to B - F/M

Product ID: USBPNLBFBM3



The USBPNLBFBM3 3ft Panel Mount USB Cable features one USB-B male connector on one end and a USB-B panel mount female port on the other, providing a convenient solution for custom enclosures (e.g. internally mounted hard drives).

Offering 3ft in cable length, the adapter allows you to extend the connection as needed within the system case.

The USBPNLBFBM3 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Add a USB-B female port to your custom enclosures

Features

- 1x USB-B male connector
- 1x USB-B panel mount female port
- Offers 3' in cable length

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	1 - USB B (4 pin)
Connector B	1 - USB B (4 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	1.5 in [3.9 cm]
Product Height	0.6 in [1.4 cm]
Weight of Product	1.7 oz [47.0 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.6 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.6 in [1.6 cm]

Shipping (Package) 1.8 oz [52.0 g]
Weight

What's in the Box

Included in Package	1 - 3 ft Panel Mount USB Cable B to B - F/M
---------------------	---

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

