

2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p - TAA

Product ID: VS221HDQ



Save time and hassle by automatically switching between your HDMI audio/video sources, using the VS221HDQ 2-Port HDMI Auto Switcher. This easy-to-use HDMI switch ensures seamless transition while switching video sources, with EDID copy maintaining your video resolution.

Ensure seamless transition while switching video sources, with EDID copy maintaining native resolution with support for 1080p. Video connection emulation ensures the settings on any connected computers are not disrupted while switching to a different video source.

Save time by connecting two HDMI video source devices to your HDMI display instead of manually connecting individual cables. Mounting hardware is also included for a tidy, professional installation.

Enjoy hassle-free operation with three different switching modes:

Automatic port selection: Enables your most recently activated video source to be displayed automatically.

Priority port selection: Prioritizes input number two above input number one. If the video source connected to input number two is activated that source will be displayed.

Manual port selection: Enables you to manually select your HDMI source with easy-to-use front panel buttons.

This product is TAA compliant and backed by a Startech.com 2 year warranty with lifetime technical support

Certifications, Reports and Compatibility



Applications

- Automatically switch between your Blu-ray player, set top box, or gaming console in a home theatre environment
- Connect and switch between two video sources on a test bench, for troubleshooting computers
- Switch between different video sources on your digital signage display in hospitals, shopping centers, or schools

Features

- Auto switching
- Priority switching
- Built-in manual control console
- EDID emulation
- Video connection emulation
- Support for video resolution up to 1080p
- Mounting hardware included

Hardware

Warranty	2 Years
AV Input	HDMI
Ports	2
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Rack-Mountable	Yes

Performance

Max Distance	10m [33ft]
Maximum Digital Resolutions	1920x1200 / 1080p
Supported Resolutions	1920x1200 1920x1080 (1080p)

1280x720 (720p)

Audio Specifications 7.1 surround sound

Connector(s)

Connector A	2 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Indicators

LED Indicators	1 - Source #1 activated
	1 - Source #2 activated

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6 A
Output Voltage	12V DC
Output Current	1.5 A
Plug Type	M
Power Consumption (In Watts)	18

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0%~80%

Physical Characteristics

Color	Black
Material	Aluminum and Plastic
Product Length	6.1 in [15.6 cm]
Product Width	2.6 in [6.5 cm]
Product Height	0.8 in [2.0 cm]

Weight of Product 10.2 oz [290.0 g]

Packaging Information

Package Quantity	1
Package Length	7.8 in [19.7 cm]
Package Width	11.7 in [29.6 cm]
Package Height	3.0 in [7.5 cm]
Shipping (Package) Weight	1.8 lb [0.8 kg]

What's in the Box

Included in Package	1 - HDMI auto switch
	1 - universal power adapter (NA, EU, UK, AU)
	1 - remote control
	1 - mounting kit
	1 - foot pad set
	1 - instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

