

4x4 HDMI Matrix Switch with Audio and Ethernet Control - 4K 60Hz - TAA

Product ID: VS424HD4K60



This 4x4 HDMI matrix switch lets you share four HDMI video sources between four independent displays or projectors, and switch between which source is active on each display device.

The HDMI switcher box provides a high level of audio and video performance, with superior contrast and crisp, clear imagery. With support for resolutions up to 4K 60Hz (4:4:4 pixel format, 8-bit color depth) and HDR, the matrix switch is ideal for conventions or trade shows, restaurants and classroom settings, as well as hospital/medical applications.

Plus, the 4K 60Hz HDMI switch is backward compatible with earlier versions of HDMI, so it's easy to use with your existing devices and displays.

This 4x4 matrix switch is equipped with convenient push-button switching, WebGUI and RS232 control, and also features a front-panel LED display for easy status monitoring.

The HDMI switch box enables you to switch each input, meaning that different A/V sources can be shown on each output, or a single source can be output to all displays.

The matrix switcher includes a remote control and IR extender module that provides simple control from a distance, and is designed to save space with a standalone or rack-mounting option (ear-mounts included).

VS424HD4K60 is backed by a StarTech.com 2 -year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Output and switch between four A/V sources across four independent displays
- Create versatile 4K digital signage
- Switch between sources and displays in training sessions

Features

- **FLEXIBLE SWITCHING:** Share and switch four HDMI inputs between four HDMI displays with this 4x4 HDMI matrix switch that lets you choose which source is active on each display device
- **UHD RESOLUTION:** This 4K 60Hz HDMI splitter supports true 4K video and HDR for uncompromising picture quality and is equipped with convenient push-button switching
- **WIDE COMPATIBILITY:** This HDMI switch box features EDID management support for greater compatibility with your video source and display
- **CONVENIENT SETUP:** Designed with space in mind this HDMI 2.0 matrix video selector features a rack-mounting option as well as a standalone option and features WebGUI and RS232 control
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this HDMI Matrix Switch is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

| | |
|--------------------|----------|
| Warranty | 2 Years |
| AV Input | HDMI |
| Ports | 4 |
| AV Output | HDMI |
| Cabling | HDMI |
| Audio | Yes |
| Rack-Mountable | Yes |
| Industry Standards | HDMI 2.0 |

Performance

| | |
|-----------------------------|---|
| Maximum Digital Resolutions | 3840 x 2160 @ 60Hz 4096 X 2160 @ 24Hz |
| Supported Resolutions | 1920 x 1200 (1080p) 3840 x 2160 (UHD 4K) |

4096 X 2160

| | |
|-----------------------|--------------------|
| Wide Screen Supported | Yes |
| Bandwidth | 18Gbps |
| Audio Specifications | 7.1 Surround Sound |
| MTBF | 404,633 Hours |

Connector(s)

| | |
|-------------------|--|
| Connector Type(s) | 1 - DB-9 (9 pin, D-Sub) 1 - RJ-45 1 - IrDA (Infrared, SIR/FIR) 1 - USB Mini (4 pin) |
| Connector A | 4 - HDMI (19 pin) |
| Connector B | 4 - HDMI (19 pin) |

Indicators

| | |
|----------------|--|
| LED Indicators | 1 - Power LED 4 - Active Port LED |
|----------------|--|

Power

| | |
|----------------|---------------------|
| Power Source | AC Adapter Included |
| Input Voltage | 100 - 240 AC |
| Input Current | 1.5 |
| Output Voltage | 24 DC |
| Output Current | 2.7 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -20C to 60C (-4F to 140F) |
| Humidity | 20-90% |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Material | Steel |
| Product Length | 17.2 in [43.7 cm] |
| Product Width | 6.3 in [16.0 cm] |
| Product Height | 1.7 in [4.3 cm] |
| Weight of Product | 4.5 lb [2.0 kg] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 18.5 in [47.0 cm] |
| Package Width | 9.4 in [23.9 cm] |
| Package Height | 3.9 in [9.9 cm] |
| Shipping (Package) Weight | 8.1 lb [3.7 kg] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1 - HDMI Matrix Switch |
| | 1 - Remote Control |
| | 1 - IR Receiver |
| | 2 - Mounting Brackets |
| | 1 - Universal Power Adapter (NA/JP, EU, UK, ANZ) |
| | 1 - User Manual |

Warranty Information

| | |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

****Product appearance and specifications are subject to change without notice.***