Bulk Cat6A Ethernet Cable, 1000ft, CMR Riser Rated, S/FTP, Pure Bare Copper, 23AWG Solid Wire, Black - TAA Compliant

Product ID: WIRC6ASCMRBK1K



This bulk Cat6a cable meets or exceeds all Category 6a cable specifications to ensure reliable 10Gb network connections. The cable is shielded to protect your network against electromagnetic interference (EMI/RFI) and system noise, providing the perfect solution for fast and safe network connections.

Each cable is tested for up to 500MHz frequency and is more than suitable for 10GBase-T Ethernet networks.

Constructed with 100% copper and foil-shielded, twisted-pair wiring, this cable was built for quality performance. The cable is designed to keep the data signals traveling through your network free from interference and is perfect in environments that are prone to large amounts of EMI.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

Each of our cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Cat6a bulk cable made from 23AWG copper is ideal for demanding Ethernet applications, facilitating Power-over-Ethernet and seamless, low-latency data transmissions.

Certifications, Reports and Compatibility

Applications

-

Features

• Enable Scalable Network Builds: Bulk Cat6A cable reliably delivers 10Gbps performance up to 500MHz, ideal for high speed servers and network drops; Supports Power over Ethernet (PoE+) for simplified connectivity to LAN access points and PoE-powered edge devices

• Ensure Consistent 10G Signaling: Maintain stable signaling in high-density environments with S/FTP shielded Cat6A cabling; Shielded cables are ideal for commercial spaces and data centers where EMI can greatly disrupt performance

• Rated for In-Wall and Riser Spaces: CMR-rated jacket meets fire safety requirements for riser installations (in-wall, between floors, elevator shafts, etc.) where compliance with building codes must be considered

• Solid Bare Copper Wire for Long Runs: Preserve signal integrity over extended distances with 23AWG solid bare copper conductors that reduce resistance; Solid wire conductors ensure uniform electrical characteristics for consistent performance in structured cabling installations

• The IT Pro's Choice: Designed for reliability in edge and on-prem deployments, our network cables are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030918183
	Package Quantity	1
	Warranty	Lifetime
Power		
	Power Delivery	90W
Physical & Environmental		
	Color	Blue
	Wire Gauge	23 AWG
	Conductor Type	Solid Copper
	Cable Length	1000.0 ft [304.8 m]
	Cable OD	0.3 in [7.4 mm]
	Product Length	1000.3 ft [304.9 m]
	Product Width	14.8 in [37.7 cm]

	Product Height	12.4 in [31.4 cm]
	Weight of Product	40.2 lb [18.2 kg]
	Operating Temperature	0C to 60C (32F to 140F)
	Storage Temperature	0C to 60C (32F to 140F)
	Humidity	70%
Performance		
	Maximum Data Transfer Rate	10 Gbps
	Cable Rating	CAT6a - 500 MHz
Hardware		
	Cable Jacket Material	PVC (Polyvinyl Chloride)
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMR (Riser)
Packaging & In-the-Box		
	Included in Package	1 - roll of Cat6A cable - Riser rated
	Package Width	15.0 in [38 cm]
	Package Depth	15.0 in [38 cm]
	Package Height	12.5 in [31.8 cm]
	Shipping (Package) Weight	42.2 lb [19.1 kg]

Product appearance and specifications are subject to change without notice.