

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Black

**Product ID:** WIRC6PATBKRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

## Certifications, Reports and Compatibility



## Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

## Features

- Available in various colors for easy identification and color-coding

---

### Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP

Cable Jacket Material PVC - Polyvinyl Chloride

Fire Rating CM Rated

**Performance**

Cable Rating CAT6 - 500 MHz

**Physical Characteristics**

Color Black

Wire Gauge 24 AWG

Conductor Type Stranded Copper

Cable Length 1000.0 ft [304.9 m]

Product Length 1000.0 ft [304.9 m]

Product Width 0.0 in [0.0 cm]

Product Height 0.0 in [0.0 cm]

Weight of Product 29.3 lb [13.3 kg]

**Packaging Information**

Package Quantity 1

Package Length 9.6 in [24.3 cm]

Package Width 15.0 in [38.2 cm]

Package Height 15.4 in [39.2 cm]

Shipping (Package) Weight 29.5 lb [13.4 kg]

**What's in the Box**

Included in Package 1 - 1000ft Roll Black Stranded Cat 6 Patch Cable

**Warranty Information**

Warranty Lifetime

*\*Product appearance and specifications are subject to change without notice.*