

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Gray

Product ID: WIRC6PATGRRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

Features

- Available in various colors for easy identification and color-coding

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP

Cable Jacket Material PVC - Polyvinyl Chloride

Fire Rating CM Rated

Performance

Cable Rating CAT6 - 500 MHz

Physical Characteristics

Color Gray

Wire Gauge 24 AWG

Conductor Type Stranded Copper

Cable Length 1000.0 ft [304.9 m]

Product Length 1000.0 ft [304.9 m]

Product Width 0.2 in [0.4 cm]

Product Height 0.2 in [0.4 cm]

Weight of Product 29.3 lb [13.3 kg]

Packaging Information

Package Quantity 1

Package Length 15.7 in [39.8 cm]

Package Width 15.3 in [38.9 cm]

Package Height 8.8 in [22.3 cm]

Shipping (Package) Weight 30.6 lb [13.9 kg]

What's in the Box

Included in Package 1000ft Roll Grey Stranded Cat 6 Patch Cable

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*