ABA.0A.250.NTL




Image for illustrative purpose only

Summary

Request a quote

audio video

Leaflet 0A en

Nb of contacts Coax	1
Locking system	Push-pull
Size	0A

Technical details

Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	0A.250 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Impedance	50 Ohms

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material	
Shell style / Model id	ABA - Adapter from LEMO receptacle to BNC plug
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	17.78 g
Environment	
Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Salt Spray Corrosion	>144 hr

Drawings



Dimensions

	A	L	S1
mm.	14.5	28.5	11
in.	0.57	1.12	0.43

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.