

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[audio video](#)[Customer Drawing](#)

Nb of contacts Coax	1
Locking system	Push-pull
Size	0A

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Solder
Insert configuration value	0A.275 - 1 Coax (75 Ohm)
Footprint IPC Class3 compatibility	No
Rated current	2 A
Impedance	75 Ohms

## Form & Material

Shell style / Model id	ABA - Adapter from LEMO receptacle to BNC plug
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	17.51 g

## Environment

Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Salt Spray Corrosion	>144 hr

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--