

Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[00and01Coaxial en](#)

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Suggested matching part	<a href="#">ERA.00.250.NTL</a>
Series	00 - NIM-CAMAC

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	00.25 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
Contact Dia.	0.7 mm (0.03in)

## Form & Material

Shell style / Model id	ABF - Adapter from LEMO plug to BNC receptacle
Housing material	Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	8.17 g

## Environment

Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
Temperature range	-55°C / +260°C (max. temperature valid for short periods of use.)
Salt Spray Corrosion	>144 hr

## Drawings



[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>
mm.	11.5	36	28
in.	0.45	1.42	1.1

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/abf-00-250-nta.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.